

## M12 FDD-602X | M12 FUEL™ sub compact 2-speed drill driver

Article: 4933459821



- Milwaukee® designed and built brushless POWERSTATE™ motor delivers more power in a more compact size.
- REDLINK PLUS™ intelligence system delivers an advanced digital overload protection for tool and battery and uniquely enhances the tool performance under load.
- REDLITHIUM-ION™ battery pack provides superior pack construction, electronics and fade-free performance to deliver more run time and more work over pack life.
- Individual battery cell monitoring optimises tool run time and ensures long term pack durability.
- 13 mm metal chuck for quick bit changes and bit retention.
- Electronic clutch with 16 torque settings and plus 1 for locked clutch drilling.
- Fuel gauge displays remaining charge.

M12 FDD-602X	
No load speed gear 1 (rpm)	0 - 450
No load speed gear 2 (rpm)	0 - 1700
Max. torque (Nm)	44
Voltage (V)	12
Battery pack capacity (Ah)	6.0
Battery type	Li-ion
Supplied in	HD Box
Charger supplied	90 min
No. of batteries supplied	2
Article Number	4933459821
Speed settings	2
Weight with battery pack (kg)	1.5
Max. drilling steel (mm)	13
Max. drilling wood (mm)	35
Chuck capacity (mm)	13