




APOT-023-06-075(0608)A-MIN

APOT SERIES THERMOELECTRIC COOLER MODULE



CERAMIC MATERIAL: Al_2O_3 / SOLDER CONSTRUCTION: 232°C, SbSn



HIGH PERFORMANCE MINIATURE THERMOELECTRIC COOLER MODULE

Features

- ROHS & REACH Compliant
- Precise temperature control
- Solid-state reliability

Applications

Laser Diodes, Optical Transceivers, Lidar Sensors, Infrared Range (IR) Sensors, CMOS Sensors, Autonomous Systems, Machine Vision, Security Cameras

CHARACTERISTICS


Hot Side Temperature	[°C]	27.0
DeltaT at 300K	[°C]	72.9
Vmax	[V]	2.7
I _{max}	[A]	1.9
Q _{max}	[W]	3.1
Elect R	[Ohms]	1.29
Length	[mm]	8.20
Width	[mm]	6.00
Height	[mm]	1.75 ± 0.127
Flatness/Parellelism	[mm]	0.05 / 0.05
Lead Length	[mm]	50.80 ± 2.00

Sealant	Colour	Temperature Range(°C)	Description
None	-	-40 to +120	-


Maximum Continuous Operating Temperature: 120°C

APOT-023-06-075(0608)A-MIN

Hot side temperature 27 degrees C



Hot side temperature 50 degrees C



APOT-023-06-075(0608)A-MIN

Hot side temperature 75 degrees C

