## CSLA2DKI

( Home : Products : Sensors : Current Sensors : Open Loop : CSLA )



CSLA Series linear current sensor, 400 A sensed current, sink or source output, through-hole, operates on AC or DC current, bottom mount

Actual product appearance may vary.

| Product Type          | Product Specifications Inductive Analog Current Sensor |  |
|-----------------------|--|--|
| **                    |  |  |
| Sensed Current Type   | ac or dc   |  |
| Sensed Current Range  | ±400 A   |  |
| Package Type          | PCB Bottom Mount                                       |  |
| Output Type           | Voltage  |  |
| Sensitivity           | 5.8 mV N* ±0.5 mV N* @ 8 Vdc                           |  |
| Supply Current        | 20 mA max.   |  |
| Offset Voltage        | Vcc/2 ±2 %   |  |
| Supply Voltage        | 6.0 Vdc to 12.0 Vdc                                    |  |
| Offset Shift          | ±0.0125  |  |
| Response Time         | 3 µs   |  |
| Operating Temperature | -25 °C to 85 °C [-13 °F to 185 °F]                     |  |
| Storage Temperature   | -40 °C to 100°C [-40 °F to 212 °F]                     |  |
| Housing Material      | PBT Polyester  |  |
| Mounting              | PCB on 3 Pins  |  |
| Pinout Style          | 3 Pin  |  |
| Availability          | Global   |  |
| Comment               | * N = Number of Turns                                  |  |
| UNSPSC Code           | 41111928   |  |
| UNSPSC Commodity      | 41111928 Current Sensors                               |  |
| Series Name           | CSLA   |  |