

PRODUCT-DETAILS

## S204M-B32

# S204M-B32 Miniature Circuit Breaker - 4P - B - 32 A



### General Information

Extended Product Type	S204M-B32
Product ID	2CDS274001R0325
EAN	4016779549882
Catalog Description	S204M-B32 Miniature Circuit Breaker - 4P - B - 32 A
Long Description	<p>System pro M compact S200M miniature circuit breakers are current limiting. They have two different tripping mechanisms, the delayed thermal tripping mechanism for overload protection and the electromechanic tripping mechanism for short circuit protection. They are available in different characteristics (B,C,D,K,Z), configurations (1P,1P+N,2P,3P,3P+N,4P), breaking capacities (up to 10 kA at 230/400 V AC) and rated currents (up to 63A). All MCBs of the product range S200M comply with IEC/EN 60898-1 and IEC/EN 609 47-2, allowing the use for residential, commercial and industrial applications. Bottom-fitting auxiliary contact can be mounted on S200M to save 50% space.</p>

### Technical

Standards	IEC/EN 60898-1 IEC/EN 60947-2
Product Name	Miniature Circuit Breaker
Tripping Characteristic	B
Rated Voltage (U <sub>r</sub> )	400 V AC
Rated Operational Voltage	acc. to IEC 60898-1 400 V AC acc. to IEC 60947-2 440 V AC
Operational Voltage	Maximum (Incl. Tolerance) 440 V AC Minimum 12 V AC Minimum 12 V DC
Rated Insulation Voltage	acc. to IEC/EN 60664-1 440 V

(U<sub>i</sub>)

Rated Impulse Withstand Voltage (U <sub>imp</sub> )	4 kV at 2000 m 5 kV at Sea Level 6.2 kV
Dielectric Test Voltage	50/60 Hz, 1 min: 2 kV
Input Voltage Type	AC/DC
Rated Current (I <sub>n</sub> )	32 A
Rated Short-Circuit Capacity (I <sub>cn</sub> )	(230 V AC) 10 kA (400 V AC) 10 kA
Rated Ultimate Short-Circuit Breaking Capacity (I <sub>cu</sub> )	(230 V AC) 25 kA (400 V AC) 15 kA (440 V AC) 15 kA
Rated Conditional Short-Circuit Current (I <sub>nc</sub> )	(230 V) 15 kA (400 V) 25 kA
Rated Service Short-Circuit Breaking Capacity (I <sub>cs</sub> )	(230 V AC) 7.5 kA
Frequency (f)	50 Hz
Rated Frequency (f)	50 / 60 Hz
Power Loss	14.8 W at Rated Operating Conditions per Pole 3.7 W
Power Supply Connection	Arbitrary
Contact Position Indication	Red ON / Green OFF
Energy Limiting Class	3
Electrical Endurance	20000 AC cycle 10000 AC cycle 20000 cycle
Number of Poles	4
Number of Protected Poles	4
Overvoltage Category	III
Product Range	S200M
Tightening Torque	2.8 N·m
Screw Terminal Type	Failsafe Bi-directional Cylinder-lift Terminal
Actuator Marking	I / O
Actuator Material	Insulation Group II, Black, Sealable
Housing Material	Insulation Group II, RAL 7035
Mounting on DIN Rail	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Mounting Position	Any
Recommended Screw Driver	Pozidriv 2
Accessories Available	Yes
Connecting Capacity	Busbar 10 / 10 mm <sup>2</sup> Flexible with Ferrule 0.75 ... 25 mm <sup>2</sup> Flexible 0.75 ... 25 mm <sup>2</sup> Rigid 0.75 ... 35 mm <sup>2</sup> Stranded 0.75 ... 35 mm <sup>2</sup>
Installation Size	acc. to DIN 43880 1
Terminal Type	Screw Terminals

## Environmental

Ambient Air Temperature	Operation -25 ... +55 °C Storage -40 ... +70 °C
Reference Ambient Air Temperature	30 °C
Degree of Protection	IP20 Enclosure with Cover IP40
Pollution Degree	3

Environmental Conditions	28 cycles with 55 °C / 90-96 % and 25 °C / 95-100 %
Resistance to Vibrations acc. to IEC 60068-2-6	5g, 20 cycles at 5 ... 150 ... 5 Hz with load 0.8 In
Resistance to Shock acc. to IEC 60068-2-27	25g / 2 shocks / 13 ms
RoHS Status	Following EU Directive 2011/65/EU
Environmental Information	2CDK400030D0201

## Technical UL/CSA

Maximum Operating Voltage UL/CSA	125 V DC 480Y/277 V AC
Interrupting Rating acc. to UL1077	(125 V DC) 10 kA (277 V AC) 6 kA (480Y / 277 V AC) 6 kA
Connecting Capacity UL/CSA	Busbar 14-8 AWG Conductor 14-4 AWG
Tightening Torque UL/CSA	18 in-lb

## Dimensions

Width in Number of Modular Spacings	4
Product Net Width	70 mm
Product Net Height	88 mm
Product Net Depth / Length	69 mm
Product Net Weight	0.5 kg
Pole Net Weight	0.115 kg
Built-In Depth (t <sub>2</sub> )	69 mm

## Container Information

Package Level 1 Units	carton 1 piece
Package Level 1 Width	92 mm
Package Level 1 Height	80 mm
Package Level 1 Depth / Length	78 mm
Package Level 1 Gross Weight	0.51 kg
Package Level 1 EAN	4016779606578
Package Level 2 Units	carton 24 piece
Package Level 2 Width	275 mm
Package Level 2 Height	210 mm
Package Level 2 Depth / Length	400 mm
Package Level 2 Gross Weight	14.44 kg
Package Level 2 EAN	4016779979979

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85362010
Country of Origin	Germany (DE)

Selling Unit of Measure

piece

---

## Certificates and Declarations (Document Number)

---

Certification Agency	EN IEC
Declaration of Conformity - CE	2CDK403001D0607
Environmental Information	2CDK400030D0201
Instructions and Manuals	2CDS207104P0001
RoHS Information	2CDK400003K0203

---



---

## Popular Downloads

---

Data Sheet, Technical Information	9AKK107046A0423
Instructions and Manuals	2CDS207104P0001
EPLAN Graphical Macro	9AKK106713A7632
EPLAN Macro	9AKK106713A7622

---



---

## Classifications

---

ETIM 6	EC000042 - Miniature circuit breaker (MCB)
ETIM 7	EC000042 - Miniature circuit breaker (MCB)
ETIM 8	EC000042 - Miniature circuit breaker (MCB)
EPLAN Catalog Tree	Electrical engineering / Protection devices / General
EPLAN Function Definition	Circuit breaker / Quadruple circuit-breaker / Quadruple circuit-breaker 1_2_3_4_5_6_7_8
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Consumer
CN8	8536 20 10
UNSPSC	39121614
eClass	V11.0 : 27141901
Object Classification Code	F

---



---

## Accessories

Identifier	Description	Type	Quantity	Unit Of Measure
2CDS200922R0001	S2C-S/H6R Signal / Auxiliary Contact	S2C-S/H6R	1	piece
2CDS200912R0001	S2C-H6R Auxiliary Contact	S2C-H6R	1	piece
2CDS200936R0001	S2C-H11L Auxiliary Contact	S2C-H11L	1	piece
2CDS200936R0002	S2C-H20L Auxiliary Contact	S2C-H20L	1	piece
2CDS200936R0003	S2C-H02L Auxiliary Contact	S2C-H02L	1	piece
2CDS200946R0001	S2C-H6-11R Auxiliary Contact	S2C-H6-11R	1	piece
2CDS200946R0002	S2C-H6-20R Auxiliary Contact	S2C-H6-20R	1	piece
2CDS200946R0003	S2C-H6-02R Auxiliary Contact	S2C-H6-02R	1	piece
2CDS200909R0001	S2C-A1 Shunt Trip	S2C-A1	1	piece
2CDS200909R0002	S2C-A2 Shunt Trip	S2C-A2	1	piece
2CSS200911R0001	S2C-UA 12 DC Undervoltage release	S2C-UA 12 DC	1	piece
2CSS200911R0002	S2C-UA 24 AC Undervoltage release	S2C-UA 24 AC	1	piece
2CSS200911R0003	S2C-UA 48 AC Undervoltage release	S2C-UA 48 AC	1	piece
2CSS200911R0004	S2C-UA 110 AC Undervoltage release	S2C-UA 110 AC	1	piece
2CSS200911R0005	S2C-UA 230 AC Undervoltage release	S2C-UA 230 AC	1	piece
2CSS200911R0006	S2C-UA 400 AC Undervoltage release	S2C-UA 400 AC	1	piece
2CSS200911R0007	S2C-UA 24 DC Undervoltage release	S2C-UA 24 DC	1	piece
2CSS200911R0008	S2C-UA 48 DC Undervoltage release	S2C-UA 48 DC	1	piece
2CSS200911R0009	S2C-UA 110 DC Undervoltage release	S2C-UA 110 DC	1	piece
2CSS200911R0010	S2C-UA 230 DC Undervoltage release	S2C-UA 230 DC	1	piece
2CSS201997R0013	S2C-CM1 Motor operating device	S2C-CM1	1	piece
2CSS203997R0013	S2C-CM2/3 Motor operating device	S2C-CM2/3	1	piece
2CSS204997R0013	S2C-CM4 Motor operating device	S2C-CM4	1	piece
GHS2001901R0003	S2C-DH Mechanical Accessories	S2C-DH	1	piece
2CSS200998R0001	S2C-BP Mechanical tripping device	S2C-BP	1	piece
2CSS200999R0001	S2C-EST Plug-in base	S2C-EST	1	piece
2CDS200918R0001	S2C-NT Hand Operated Neutral	S2C-NT	1	piece
2CCA880100R0001	CMS-100PS Sensor	CMS-100PS	1	piece
2CCA880101R0001	CMS-101PS Sensor	CMS-101PS	1	piece
2CCA880102R0001	CMS-102PS Sensor	CMS-102PS	1	piece

## Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Miniature Circuit Breakers MCBs

