

DIAZED FUSE LINK 500V QUICK-RESPONSE



Similar to image

**Technical data:**

<b>Color coding of the fuse link</b>		gray
<b>Current / for AC / rated value</b>	A	16
<b>Tripping characteristic class</b>		quick acting (F)
<b>Size of the fallback-system / acc. to DIN EN 60269-1</b>		DII
<b>Supply voltage</b>		
• for AC / rated value	V	500
• for DC	V	500
<b>Switching capacity current</b>		
• in accordance with IEC 60947-2 / rated value	kA	50
• with DC / in accordance with IEC 60947-2 / rated value	kA	8
<b>Ambient temperature</b>		
• minimum	°C	-5
• maximum	°C	40

**Certificates/approvals:**

General Product Approval	Declaration of Conformity	Test Certificates
<a href="#">ROSTEST</a>	<a href="#">Manufacturer</a>	<a href="#">Manufacturer</a>

**Further information:**

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/lowvoltage/mall>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**


<http://support.automation.siemens.com/WW/view/en/5SB161/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SB161](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SB161)

**CAX-Online-Generator**

<http://www.siemens.com/cax>



last change:

Aug 26, 2011