



## IP66 13A Switch Spur with Neon

### Description

Weathersafe has been designed to withstand the toughest outdoor and demanding environments, combining reliability and long-lasting performance with a sleek black finish. Rated IP66 and manufactured from impact-resistant polycarbonate ensures the product endures harsh conditions, making it an ideal solution for gardens, patios, and workshops.

This switched spur is 13A rated with a neon indicator as a status indicator, and has captive and backed out terminals with large cable lead-ins and clear markings.

Installation is quick and effortless. Fast-fix captive screws allow the detachable back box to be removed with ease, while mounting points are separated from the main wiring space minimising the need for weatherproof sealant to reinstate IP66 rating.

### Features

- IP66 rated protects against dust and powerful water jets, ideal for tough indoor and outdoor environments.
- Pre-fitted with a double pole switched spur with neon indicator featuring clear terminal markings, twin earth terminals, top-facing captive screws, and large cable lead-ins.
- Single latching clip provides quick and easy access to the accessory
- Translucent cover allows neon indicators to be seen when closed with locking points on cover allow use of a padlock to restrict access
- Grey impact resistant polycarbonate housing
- Fast fix screws allows accessory frame to be quickly installed and removed
- Back box mounting points separated from main wiring space to maintain IP rating
- Multiple drill out cable entry points on all sides and rear of back box

### Product Code

**IP66 13A Switch Spur with Neon**      TW1371

### Technical Specification

- **Input Voltage** - 220-240VAC, 50/60Hz
- **Maximum Load** - 3120W, 13A
- **Material** - Polycarbonate
- **IP Rating** - IP66
- **Terminal Capacity** - 4 x 2.5mm<sup>2</sup>
- **Overall Outer Dimensions (W x H x D)** - 128 x 177 x 90mm

### Compliance

- BS 1363-4
- BS EN 60529

### Guarantee

- 10-year guarantee