

COAXIAL ADAPTER, 4.3-10 - 7/16, 50 Ohm, plug / plug (male / male)

32_4310-716-50-X1/133_W

Properties

- Precision interfaces
- Excellent electrical performance
- Premium base materials and platings



Product configuration		
Interface type	Gender	Standard
4.3-10	plug (male)	IEC 61169-54
7/16	plug (male)	IEC 61169-4_CECC 22190_DIN 47223_VG 95250

Interface and material data		
4.3-10		
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
7/16		
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating
Body		SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating

Electrical data	
Impedance	50 Ω
Interface frequency	7.5 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 4 GHz	27 dB	1.094

COAXIAL ADAPTER, 4.3-10 - 7/16, 50 Ohm, plug / plug (male / male)

32_4310-716-50-X1/133_W

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
4 GHz ... 6 GHz	25 dB	1.119

Mechanical data	
Weight	0.117 kg
Mating cycles	500

Environmental data	
Operation temperature	-55 °C ... 90°C

Ordering Information Table		
Item number	Item description	Packaging type
85017233	32_4310-716-50-X1/133_WE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2357 / Date of publication: 26.11.2023 / uncontrolled copy