

# Panel feed-through terminal block - HDFKV 10 GNYE - 0709291

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Panel feed-through terminal block, Connection method: Screw connection, Number of positions: 1, Color: green-yellow

The figure shows a version of the article



## Key commercial data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 017918 005016
Weight per Piece (excluding packing)	21.29 g
Custom tariff number	85369010
Country of origin	Greece

## Technical data

### General

Color	green-yellow
Number of positions	1

### Connection data

Connection method	Screw connection
-------------------	------------------

## Classifications

### eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141134
eCl@ss 5.1	27141134
eCl@ss 6.0	27141134
eCl@ss 7.0	27141134

# Panel feed-through terminal block - HDFKV 10 GNYE - 0709291

## Classifications

### eCl@ss

eCl@ss 8.0	27141134
------------	----------

### ETIM

ETIM 2.0	EC001283
ETIM 3.0	EC001283
ETIM 4.0	EC001283
ETIM 5.0	EC001283

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

## Approvals

### Approvals

---

### Approvals

CSA / UL Recognized / KEMA-KEUR / cUL Recognized / PRS / IECCE CB Scheme / EAC / cULus Recognized

---

### Ex Approvals

---

### Approvals submitted

---

### Approval details

CSA	
mm <sup>2</sup> /AWG/kcmil	22-6
Nominal current I <sub>N</sub>	65 A
Nominal voltage U <sub>N</sub>	300 V

# Panel feed-through terminal block - HDFKV 10 GNYE - 0709291

## Approvals

UL Recognized			
		B	D
mm <sup>2</sup> /AWG/kcmil	24-6	24-6	24-6

KEMA-KEUR	
mm <sup>2</sup> /AWG/kcmil	10
Nominal current I <sub>N</sub>	57 A
Nominal voltage U <sub>N</sub>	250 V

cUL Recognized			
		B	D
mm <sup>2</sup> /AWG/kcmil	24-6	24-6	24-6

PRS
-----

IECEE CB Scheme	
mm <sup>2</sup> /AWG/kcmil	10
Nominal current I <sub>N</sub>	57 A
Nominal voltage U <sub>N</sub>	250 V

EAC
-----

cULus Recognized	
------------------	--