


06110050

RCK 11 - Self centring

2D Technical Drawing

Dynamic 3D View
Technical Specifications

Part number (CODE)	06110050
Ød (DD) mm	50
ØD (D) mm	80
L1 (L1) mm	56
L2 (L2) mm	64
L (L) mm	72
Maximum torque Mt (MT) N/mm ²	4150
Clamping pressure - Shaft (CPS) N/mm ²	200
Clamping pressure - Hub (CPH)	98
Clamping pressure - N° (CPN)	8
Clamping screws DIN 912 MAT. 12.9 - Type (CSTY) mm	M8x50
Clamping screws DIN 912 MAT. 12.9 - Torque (CSTO)	41
Extraction thread - Type (ETT) mm	M8
Extraction thread - N° (ETN)	3
Weight (WEIGHT) kg	1.30