

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,1998

© COPYRIGHT 2011APR BY-Tyco Electronics Japan G.K.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD






D

REVISED

25APR11

MM

NY

1318126-1/-2/-3 : AS SHOWN
9-1318126-2RECOMENDED PC BOARD HOLE PATTERN(TOL:±0.05)
PC BOARD THICKNESS:1.6±0.3
(CONNECTOR MOUNT SIDE)9-1318126-2
1318126-2
(KEYING Y)
SCALE:2-11318126-3
(KEYING Z)
SCALE:2-1

NOTES


1. MATERIAL:HOUSING:GLASS FIELED THERMO PLASTIC
,POLYESTER(94V-0),
COLOR: 1318126-1/-2/-3 : BLACK
9-1318126-2 : NATURAL

TAB CONTACT:COPPER ALLOY

RETENTION LEG:BRASS


- 2 FINISH(CONTACT AREA):0.38μmMIN GOLD PLATING
OVER NI PLATING

- 3 FINISH(RETENTION LEG): TIN PLATED
(CONTACT TAIL) OVER NICKEL



Y	BLACK	SEQUENTIAL SHEET2	1-1318126-2
X	BLACK	SEQUENTIAL SHEET2	1-1318126-1
Z	BLACK	NORMAL	1318126-3
Y	NATURAL	NORMAL	9-1318126-2
Y	BLACK	NORMAL	1318126-2
X	BLACK	NORMAL	1318126-1
KEY	COLOR	TYPE	PART NO

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED	DWN K.IKEDA 7/DEC/'98	TE Connectivity	
mm		100 ±0.3 300 >10 : ±0.35 1000 >30 : ±0.4 ANGLE : ±3°	CHK N.MATSUBARA 7/DEC/'98 APVD I.HASEGAWA 7/DEC/'98 PRODUCT SPEC 108-5619 APPLICATION SPEC 114-5258 WEIGHT		
MATERIAL		FINISH	CUSTOMER DRAWING	SIZE A3	CAGE CODE 00779
SEE NOTES		SEE NOTES	SCALE 4-1	DRAWING NO C-1318126	RESTRICTED TO -
			SHEET 1 OF 2	REV D	




LOC		DIST		REVISIONS					
P	LTR	DESCRIPTION		ECN	DATE	DWN	APVD		
		SEE SHEET 1							

1-1318126-1,2;AS SHOWN
SEQUENTIAL TYPE


		CIRCUIT NO					
R O W	B	①	②	②	②	②	②
	A	②	②	②	②	②	①

POINT OF SEQUENTIAL
1-1318126-1,2

- NOTES
1. MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC
POLYESTER(94V-0),COLOR:BLACK
- TAB CONTACT:COPPER ALLOY
RETENTION LEG:BRASS
2. FINISH(CONTACT AREA):0.38μmMIN GOLD PLATING
OVER Ni PLATING
3. FINISH(RETENTION LEG): TIN PLATED
(CONTACT TAIL) OVER NICKEL



1-1318126-1
(KEYING X)
SCALE:2-1

		DWN K.IKEDA 7/DEC/'98 CHK N.MATSUBARA 7/DEC/'98 APVD I.HASEGAWA 7/DEC/'98 PRODUCT SPEC 108-5619 APPLICATION SPEC 114-5258 WEIGHT T1		TE Connectivity					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED 100 ±0.3 300 >10 ±0.35 1000 >30 ±0.4 ANGLE ±3°		NAME DOUBLE ROW HEADER ASS'Y 12P ("V"TYPE) <DYNAMIC D-2100D>					
									
MATERIAL SEE NOTES		FINISH SEE NOTES		SIZE A3	CAGE CODE 00779	DRAWING NO C-1318126	RESTRICTED TO —		
CUSTOMER DRAWING						SCALE 4-1	SHEET 2	OF 2	REV D