

## Base strip - EMSTBV 2,5/12-GF-5,08 - 1915314

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Header, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 12, Pitch: 5.08 mm, Color: green, Contact surface: Tin, Mounting: Press-in



The figure shows a 10-position version of the product

### Why buy this product

- ✓ Press-in tools available on request
- ✓ Pin strips with ERNI-PRESS flexible press-in zone
- ✓ Processing according to EN 60352-5



### Key commercial data

|                                      |                                                                                      |
|--------------------------------------|--------------------------------------------------------------------------------------|
| Packing unit                         | 50 pc                                                                                |
| Minimum order quantity               | 50 pc                                                                                |
| GTIN                                 |  |
| Weight per Piece (excluding packing) | 6.03 g                                                                               |
| Custom tariff number                 | 85366990                                                                             |
| Country of origin                    | Germany                                                                              |
| Note                                 | Made to Order (non-returnable)                                                       |

### Technical data

#### Dimensions

|                |          |
|----------------|----------|
| Length         | 8.6 mm   |
| Pitch          | 5.08 mm  |
| Dimension a    | 55.88 mm |
| Pin dimensions | 1,7 mm   |
| Hole diameter  | 1.75 mm  |

#### General

|                             |                  |
|-----------------------------|------------------|
| Range of articles           | EMSTBV 2,5/..-GF |
| Insulating material group   | IIIa             |
| Rated surge voltage (III/3) | 4 kV             |

## Base strip - EMSTBV 2,5/12-GF-5,08 - 1915314

### Technical data

#### General

|                                         |        |
|-----------------------------------------|--------|
| Rated surge voltage (III/2)             | 4 kV   |
| Rated surge voltage (II/2)              | 4 kV   |
| Rated voltage (III/3)                   | 200 V  |
| Rated voltage (III/2)                   | 320 V  |
| Rated voltage (II/2)                    | 320 V  |
| Connection in acc. with standard        | EN-VDE |
| Nominal current $I_N$                   | 12 A   |
| Maximum load current                    | 12 A   |
| Insulating material                     | PBT    |
| Inflammability class according to UL 94 | V0     |
| Color                                   | green  |
| Number of positions                     | 12     |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 272607xx |
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27260701 |
| eCl@ss 6.0 | 27260704 |
| eCl@ss 7.0 | 27440402 |
| eCl@ss 8.0 | 27440402 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC002637 |
| ETIM 5.0 | EC002637 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211810 |
| UNSPSC 7.0901 | 39121409 |
| UNSPSC 11     | 39121409 |
| UNSPSC 12.01  | 39121409 |
| UNSPSC 13.2   | 39121409 |

### Approvals

#### Approvals

---

## Base strip - EMSTBV 2,5/12-GF-5,08 - 1915314

### Approvals

#### Approvals

UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / IEC EE CB Scheme / CCA / EAC / cULus Recognized

#### Ex Approvals

#### Approvals submitted

#### Approval details

|                                                                                                 |       |       |
|-------------------------------------------------------------------------------------------------|-------|-------|
| UL Recognized  |       |       |
|                                                                                                 | B     | D     |
| Nominal current I <sub>N</sub>                                                                  | 12 A  | 10 A  |
| Nominal voltage U <sub>N</sub>                                                                  | 300 V | 300 V |

|                                                                                                                             |       |
|-----------------------------------------------------------------------------------------------------------------------------|-------|
| VDE Gutachten mit Fertigungsüberwachung  |       |
|                                                                                                                             |       |
| Nominal current I <sub>N</sub>                                                                                              | 12 A  |
| Nominal voltage U <sub>N</sub>                                                                                              | 250 V |

|                                                                                                    |       |       |
|----------------------------------------------------------------------------------------------------|-------|-------|
| cUL Recognized  |       |       |
|                                                                                                    | B     | D     |
| Nominal current I <sub>N</sub>                                                                     | 12 A  | 10 A  |
| Nominal voltage U <sub>N</sub>                                                                     | 300 V | 300 V |

|                                                                                                     |       |
|-----------------------------------------------------------------------------------------------------|-------|
| IECEE CB Scheme  |       |
|                                                                                                     |       |
| Nominal current I <sub>N</sub>                                                                      | 12 A  |
| Nominal voltage U <sub>N</sub>                                                                      | 250 V |

|                                |      |
|--------------------------------|------|
| CCA                            |      |
|                                |      |
| Nominal current I <sub>N</sub> | 12 A |

## Base strip - EMSTBV 2,5/12-GF-5,08 - 1915314

### Approvals

|                    |       |
|--------------------|-------|
| Nominal voltage UN | 250 V |
|--------------------|-------|

|     |
|-----|
| EAC |
|-----|

|                                                                                                    |
|----------------------------------------------------------------------------------------------------|
| cULus Recognized  |
|----------------------------------------------------------------------------------------------------|

### Accessories

#### Accessories

#### Coding element

Coding star - CR-MSTB - 1734401



Coding section, inserted into the recess in the header or the inverted plug, red insulating material

#### Filler plug

Accessories - MSTB-BL - 1755477



Keying cap, for forming sections, plugs onto header pin, green insulating material

#### Labeled terminal marker

Marker card - SK 5,08/3,8:FORTL.ZAHLEN - 0804293



Marker card, Card, white, labeled, Horizontal: Consecutive numbers 1 - 10, 11 - 20, etc. up to 91 - (99)100, Mounting type: Adhesive, for terminal block width: 5.08 mm, Lettering field: 5.08 x 3.8 mm

#### Mounting material

## Base strip - EMSTBV 2,5/12-GF-5,08 - 1915314

### Accessories

#### Assembly adapters - EMSTBVA 2,5-SS-1-5,08 - 1877216



Stamp set, consisting of an upper and lower stamp, upper stamp: 2 to 16-pos., lower stamp: 2 to 24-pos., pitch: 5.08 mm

---

#### Accessories - EMSTBVA 2,5-SS-2-5,08 - 1877229

Stamp set, consisting of an upper and lower stamp, upper stamp: 17 to 24-pos., lower stamp: 2 to 24-pos., pitch: 5.08 mm

---

#### Accessories - EMSTB 2,5-SH - 1877203



Stamp holder, for upper and lower stamp

---

#### - EMSTBVA 2,5-SS-3-5,0 - 1914810

Stamp set, consisting of an upper and lower stamp, upper stamp: 17 to 24-pos., lower stamp: 2 to 24-pos., pitch: 5.0 mm

---

### Additional products


#### Printed-circuit board connector - MVSTBR 2,5/12-STF-5,08 - 1835193



Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 12, Pitch: 5.08 mm, Connection method: Screw connection, Color: green, Contact surface: Tin

---

#### Printed-circuit board connector - QC 1/12-STF-5,08 - 1883459




Plug component, Nominal current: 10 A, Rated voltage (III/2): 630 V, Number of positions: 12, Pitch: 5.08 mm, Connection method: Insulation displacement connection QUICKON, Color: green, Contact surface: Tin

## Base strip - EMSTBV 2,5/12-GF-5,08 - 1915314

### Accessories

#### Printed-circuit board connector - FKCVR 2,5/12-STF-5,08 - 1874206



Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 12, Pitch: 5.08 mm, Connection method: Spring-cage connection, Color: green, Contact surface: Tin

---

#### Printed-circuit board connector - FKCVW 2,5/12-STF-5,08 - 1873906



Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 12, Pitch: 5.08 mm, Connection method: Spring-cage connection, Color: green, Contact surface: Tin

---

#### Printed-circuit board connector - FKC 2,5/12-STF-5,08 - 1873304



Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 12, Pitch: 5.08 mm, Connection method: Spring-cage connection, Color: green, Contact surface: Tin

---

#### Printed-circuit board connector - MVSTBW 2,5/12-STF-5,08 - 1835009



Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 12, Pitch: 5.08 mm, Connection method: Screw connection, Color: green, Contact surface: Tin

---

#### Printed-circuit board connector - MSTBC 2,5/12-STZF-5,08 - 1809831



Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 12, Pitch: 5.08 mm, Connection method: Crimp connection, Color: green, Corresponding female crimp contacts with current [A] and conductor cross section range [mm²] data: 10A/MSTBC-MT 0,5-1,0 (3190564); 10A/MSTBC-MT 0,5-1,0 BA (3190645); 12A/MSTBC-MT 1,5-2,5 (3190551); 12A/MSTBC-MT 1,5-2,5 BA (3190658). BA = Bandkontakte

## Base strip - EMSTBV 2,5/12-GF-5,08 - 1915314

### Accessories

Printed-circuit board connector - MSTBT 2,5/12-STF-5,08 - 1805398

Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 12, Pitch: 5.08 mm, Connection method: Screw connection, Color: green, Contact surface: Tin



Printed-circuit board connector - MSTB 2,5/12-STF-5,08 - 1778085

Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 12, Pitch: 5.08 mm, Connection method: Screw connection, Color: green, Contact surface: Tin



Printed-circuit board connector - FKCT 2,5/12-STF-5,08 - 1902408

Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 12, Pitch: 5.08 mm, Connection method: Spring-cage connection, Color: green, Contact surface: Tin




Printed-circuit board connector - FRONT-MSTB 2,5/12-STF-5,08 - 1777895

Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 12, Pitch: 5.08 mm, Connection method: Screw connection, Color: green, Contact surface: Tin




### Drawings

Drilling diagram





Dimensioned drawing



## Base strip - EMSTBV 2,5/12-GF-5,08 - 1915314

Drilling diagram


**Bore hole in the basic material,**  
mostly epoxy glass fabric FR4 or EP-GC



**Bore hole with Cu ferrule**

Drilling diagram

**Bore hole with Cu ferrule**



Drilling diagram

**Plated-through bore hole with Sn/SnPb**

