

Product data sheet

Specifications



Repacked, fixing frame, Mureva Styl, 2 gangs, vertical, anthracite

MUR34151W



This repacked option saves 0.26 over the standard condition

Main

Range of product	Mureva Styl
Product or component type	Fixing frame
Range compatibility	Mureva Styl
Colour tint	Anthracite (RAL 7016)

Complementary

Device mounting	Flush
Number of gangs	2 gangs
Installation direction	Vertical
Condition of use	Indoor/outdoor
Material	PC
fixing mode	By screws
Surface finish	Matt
surface treatment	Untreated
Distance between centers	71 mm
Length	84 mm
Height	155 mm
Width	84 mm
Depth	23 mm
Projecting depth	19 mm
Chemical and detergent products resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Quality labels	AENOR NF
IP degree of protection	IP55
IK degree of protection	IK08
Flame retardance	Self-extinguishing 650 °C conforming to IEC 60695-2-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-25...55 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	8.200 cm
Package 1 Length	15.400 cm
Package 1 Weight	63.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	8.000 cm
Package 2 Width	16.000 cm
Package 2 Length	39.500 cm
Package 2 Weight	409.000 g
Unit Type of Package 3	S04
Number of Units in Package 3	30
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	3.174 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.3 kg CO2 eq.

Use Better



Materials and Substances

SCIP Number

59bc1733-7007-4ba6-bfd5-f7904c7d9a13

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No