



SAFETY DATA SHEET
SAPPHIRE HI-SPEED 2

Page: 1
Compilation date: 10/09/2014
Revision date: 05/02/2016
Revision No: 5

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: SAPPHIRE HI-SPEED 2

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: PC24: Lubricants, greases, release products.

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

Tel: +44 (0) 113 232 2700

Fax: +44 (0) 113 232 2740

Email: customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: This product has no classification under CLP.

2.2. Label elements

Label elements: This product has no label elements.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

SAFETY DATA SHEET

SAPPHIRE HI-SPEED 2

Page: 2

Hazardous ingredients:

PROPRIETARY CORROSION PREVENTATIVE

EINECS	CAS	PBT / WEL	CLP Classification	Percent
260-991-2	57855-77-3	-	Skin Irrit. 2: H315; Eye Irrit. 2: H319	<1%

2-ETHYLHEXYL ZINC DITHIOPHOSPHATE

224-235-5	4259-15-8	-	Eye Dam. 1: H318; Aquatic Chronic 2: H411	<1%
-----------	-----------	---	---	-----

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes.

Ingestion: Wash out mouth with water.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: No symptoms.

4.3. Indication of any immediate medical attention and special treatment needed

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Use water spray to cool containers. Suitable extinguishing media for the surrounding fire should be used.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

[cont...]

SAFETY DATA SHEET

SAPPHIRE HI-SPEED 2

Page: 3

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

PROPRIETARY CORROSION PREVENTATIVE

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	5mg/m ³	10mg/m ³	-	-

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Respiratory protection: Respiratory protection not normally required.

Hand protection: Gloves (oil-resistant).

Eye protection: Safety glasses with side-shields.

Skin protection: Oil-resistant protective clothing.

Environmental: Prevent from entering in public sewers or the immediate environment.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Paste

Colour: Beige

Odour: Odourless

Evaporation rate: Negligible

Oxidising: Non-oxidising (by EC criteria)

[cont...]

SAFETY DATA SHEET

SAPPHIRE HI-SPEED 2

Page: 4

Solubility in water: Insoluble

Viscosity: Highly viscous

Boiling point/range°C: No data available.

Melting point/range°C: No data available.

Flash point°C: > 180

Autoflammability°C: > 180

Relative density: < 1

pH: Approx. 7

VOC g/l: 0

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong reducing agents.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

2-ETHYLHEXYL ZINC DITHIOPHOSPHATE

DERMAL	RBT	LD50	>5000	mg/kg
ORAL	RAT	LD50	>3100	mg/kg

Toxicity values: No data available.

Symptoms / routes of exposure

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: No symptoms.

[cont...]

SAFETY DATA SHEET

SAPPHIRE HI-SPEED 2

Page: 5

Section 12: Ecological information

12.1. Toxicity

Hazardous ingredients:

2-ETHYLHEXYL ZINC DITHIOPHOSPHATE

ALGAE	72H ErC50	>240	mg/l
DAPHNIA	48H EC50	1 - 10	mg/l
FISH	96H LC50	1 - 10	mg/l

12.2. Persistence and degradability

Persistence and degradability: Only slightly biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Non-volatile. Absorbed only slowly into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

Transport class: This product does not require a classification for transport.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

Compiled in accordance with REACH.

[cont...]

SAFETY DATA SHEET

SAPPHIRE HI-SPEED 2

Page: 6

Phrases used in s.2 and s.3: H315: Causes skin irritation.
H318: Causes serious eye damage.
H319: Causes serious eye irritation.
H411: Toxic to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.

