


O6T215



Diffuse reflection sensor

O6TIFPKG/AS/4P



- 1: output function switch
2: potentiometer sensitivity receiver in upper lens
transmitter in lower lens



Product characteristics		
Type of light		infrared light
Housing		rectangular
Application		
Function principle		Diffuse reflection sensor
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	16; ((24 V))
Protection class		III
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[nm]	850
Outputs		
Electrical design		PNP
Output function		light-on/dark-on mode; (selectable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	1000
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Detection zone		
Range	[mm]	5...600; (white paper 200 x 200 mm 90% remission)



Diffuse reflection sensor

O6TIFPKG/AS/4P

Setting range	[mm]	100...600
Range adjustable		yes
Max. light spot diameter	[mm]	24
Light spot dimensions refer to		at maximum range

Operating conditions

Ambient temperature	[°C]	-25...60
Protection		IP 65; IP 67

Tests / approvals

EMC		EN 60947-5-2	
MTTF	[years]		898
UL approval		UL Approval no.	E001

Mechanical data

Weight	[g]	19
Housing		rectangular
Dimensions	[mm]	46 x 13 x 21
Materials		housing: ABS; PPSU
Lens material		PMMA
Lens alignment		side lens
Sealing material		EPDM
Tightening torque	[Nm]	0.5

Displays / operating elements

Display	switching status	1 x LED, yellow
	operation	1 x LED, green

Remarks

Remarks	operating voltage "supply class 2" according to cULus
Pack quantity	1 pcs.

Electrical connection


Connector: 1 x M8; coding: A; Locking: brass, coated; Sealing: EPDM



Diffuse reflection sensor

O6TIFPKG/AS/4P

Connection



Diagrams and graphs

excess gain graph

