



 PRODUCT-DETAILS

MLBL-08R

MLBL-08R LED block



General Information

Extended Product Type	MLBL-08R
Product ID	1SFA611621R1081
EAN	7320500544914
Catalog Description	MLBL-08R LED block

Long Description	<p>The MLBL-08R LED block is: - Red - Illuminated - Front mounting - 380 V</p> <p>This LED block is part of ABB's modular plastic range, the most versatile range with a high level of flexibility and market-leading electrical ratings. Engineered for total reliability, longer lifetime, and highest mechanical durability. Self-cleaning contacts ensure reliable operation without the need for maintenance, increasing uptime. A high degree of protection guarantees reliability in extreme environments. The innovative design simplifies the entire process, from selection to easy and quick, tool-free installation. The perfect solution for every application.</p>
------------------	--

Ordering

Minimum Order Quantity	10 piece
Customs Tariff Number	85369001

Popular Downloads

Data Sheet, Technical Information	1SFC151007C02__
Instructions and Manuals	1SFC151011M0201

Dimensions

Product Net Width	0.01 m
Product Net Height	0.044 m
Product Net Depth / Length	0.042 m
Product Net Weight	0.01 kg

Technical

Ambient Air Temperature	Operation -25 ... +70 °C Storage -40 ... +85 °C
Color	Red
Illumination	Illuminated
Lamp Type	380 V AC, integrated LED
Mounting Type	Front mounting
Rated Frequency (f)	50 / 60 Hz
Rated Operational Voltage	380 V AC
Connecting Capacity	Flexible with Ferrule 1 x 0.75...2.5 mm ² Flexible with Ferrule 2 x 0.75...2.5 mm ² Flexible with Insulated Ferrule 1 x 0.75...2.5 mm ² Flexible with Insulated Ferrule 2 x 0.75...2.5 mm ² Flexible 1 x 0.75 ... 2.5 mm ² Flexible 2 x 0.75 ... 2.5 mm ² Solid 1 x 0.75...2.5 mm ² Solid 2 x 0.75...2.5 mm ²
Connection Type	Screw Clamp
Terminal Type	Screw Terminals
Tightening Torque	0.9 N·m
Wire Stripping Length	8 mm
Suitable For	MCBH-00 MCBH5-00 MP1 MP2 MP3 MP4 MPMT3 MPMP3 M2SS1 M2SS2 M2SS3 M2SS4 M2SS5 M2SS6 M3SS1 M3SS2 M3SS3 M3SS4 M3SS5 M3SS6 M3SS7 M3SS8 MPM1

Suitable for Product

Pilot Devices

Class

Technical UL/CSA

Connecting Capacity	1x 18...14 AWG
UL/CSA	2x 18...14 AWG

Environmental

Degree of Protection	Terminals IP20
----------------------	----------------

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	2CMT2022-006479
RoHS Declaration	2CMT2022-006498
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	2CMT2023-006523
WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Certificates and Declarations

CB Certificate	SEMKO_SE-56219
CQC Certificate	CQC2008010305274953
cULus Certificate	9AKK107046A9925
Declaration of Conformity - CCC	2020980305001106
Declaration of Conformity - CE	2CMT2015-005452
Declaration of Conformity - UKCA	2CMT2020-006121
DNV GL Certificate	E-14107
EAC Certificate	1SFC150017D1101

Container Information

Package Level 1 Units	bag 10 piece
Package Level 1 Width	0.135 m
Package Level 1 Depth / Length	0.155 m
Package Level 1 Height	0.025 m
Package Level 1 Gross Weight	0.11 kg
Package Level 1 EAN	7320500372845

External Classifications and Standards

Object Classification Code	E
----------------------------	---

ETIM 6	EC000204 - Lamp holder block for control circuit devices
ETIM 7	EC000204 - Lamp holder block for control circuit devices
ETIM 8	EC000204 - Lamp holder block for control circuit devices
eClass	V11.0 : 27371209
UNSPSC	39122221
IDEA Granular Category Code (IGCC)	5219 >> Switch part or accessory
E-Number (Finland)	2315780
E-Number (Sweden)	3705628

Categories

Low Voltage Products and Systems → Control Products → Pilot Devices → Accessories

Low Voltage Products and Systems → Control Products → Pilot Devices → Modular Plastic Range

