

LG8K06Q706

Enclosed reversing starter, TeSys
LG, 1-1.6A, 380/400V AC coil, including 2
LC1K, GV2ME, pushbutton, 2-pos switch

Main

Range	TeSys
Product name	TeSys LG
Device short name	LG8K
Product or component type	Enclosed DOL reversing starter
Device application	Safety
Utilisation category	AC-3
Device composition	Reversing contactor Circuit-breaker
Motor power kW	0.25 kW at 220/230 V AC 50/60 Hz 0.55 kW at 400/415 V AC 50/60 Hz 0.55 kW at 440 V AC 50/60 Hz
Thermal protection adjustment range	1...1.6 A
[Uc] control circuit voltage	380/400 V AC 50/60 Hz
Control type	Push-button stop black O Selector switch 2 positions start black I-II Mushroom head push-button emergency stop red

Complementary

Width	175 mm
Height	165 mm
Depth	146 mm
Net weight	1.64 kg
Cable entry number	4 2 Pg 13 + 2 Pg 16 top 4 2 Pg 13 + 2 Pg 16 bottom

Environment

Standards	IEC 60204-1 IEC 60947-4-1
Product certifications	CE[RETURN]UKCA
IP degree of protection	IP55 conforming to IEC 60529 (for enclosure)
IK degree of protection	IK07 conforming to IEC 60529
Material	Polycarbonate
Environmental characteristic	Standard environment

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins