



Connectors > Power Connectors > Circular Power > Circular Power Connectors



Number of Positions: 9

Connector Product Type: **Housing**

Operating Voltage: **250 VDC**

Wire Size: **.0509 – .823 mm²**

Features

Product Type Features

Connector Seal & Plug Type	Peripheral, Wire Entry Seal
Connector Product Type	Housing
Connector System	Wire-to-Wire
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Receptacle
Circular Connector Shell Type	All Plastic

Configuration Features

Reverse Numbering	Without
Number of Positions	9
Number of Power Positions	0
Number of Signal Positions	9

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------



Contact Features

Reverse Gender	No
Contact Type	Pin
Contact Current Rating (Max)	5.9 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Mating Retention Type	Threaded Coupling
Thread Size	3/4-20 UNEF-2A
Mating Alignment	With
Connector Mounting Type	Panel Mount
Mating Retention	With
Panel Mount Feature	With

Housing Features

Housing Color	Black
Housing Material	Thermoplastic
Circular Connector Shell Size	11

Dimensions

Compatible Insulation Diameter Range	.89 – 1.5 mm [.035 – .059 in]
Wire Size	.0509 – .823 mm²

Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
Fluid Resistance	Immersion

Operation/Application

Circuit Application	Power & Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	100
Packaging Method	Carton



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


TE Part # 770988-1
MINI UMNL SOK 22-18AWG SN LP

TE Part # 1546921-1
STR RLF ASSY,TUBING,SIZE 11




TE Part # 1445807-1
PLUG,11-9,SM INS,STD KEY

TE Part # 1445807-3
PLUG,11-9,LG INS,STD KEY



 TE Part # 1-770901-0 MINI UMNL PIN 26-22 AWG AU LF	 TE Part # 1-770903-0 MINI UMNL PIN 22-18 AWG AU	 TE Part # 1-794058-0 MINI UMNL SOK L/P LF	 TE Part # 1-770904-0 MINI UMNL SOK 22-18 AWG AU
 TE Part # 1-770986-0 MINI UMNL SOK 26-22AWG AU LP	 TE Part # 1-770987-0 MINI UMNL PIN 22-18 AWG AU LP	 TE Part # 770834-4 MINI UMNL SOCKET PHBR	 TE Part # 770902-3 MINI UMNL SOK 26-22 AWG AU
 TE Part # 770902-6 MINI UMNL SOK 26-22 AWG AU	 TE Part # 770903-6 MINI UMNL PIN 22-18 AWG AU	 TE Part # 1-770834-1 MINI UMNL SOK PHBRZ AU LF	 TE Part # 1-2407269-2 CAP, CPC, SIZE 11 RECP & 13 PLUG, BLACK
 TE Part # 1546746-4 R/A CABLE CLAMP KIT,SZ 11, MINI CPC	 TE Part # 1604089-2 CAP,DUST,SIZE 11	 TE Part # 1-770988-1 MINI UMNL SOK 22-18AWG LP LF	 TE Part # 1-770902-0 MINI UMNL SOK 26-22 AWG AU

Also in the Series | AMP Circular Plastic Connectors

 Circular Power Connectors(40)	 Connector Backshells(1)	 Connector Caps & Covers(16)	 Connector Seals & Cavity Plugs(35)
--	---	--	---




Connector Strain Relief(60)



Insertion & Extraction Tools(1)

Also in the Series | Mini Circular Plastic Connectors



Circular Power Connectors(40)




Connector Contacts(20)




Power Contacts(20)

Customers Also Bought




TE Part #1445823-3
REC,11-6,FLNG MT,LG INS,STD KE



TE Part #1445816-3
RECPT,11-9,FLNG MT,STD KEY




TE Part #1-770902-0
MINI UMNL SOK 26-22 AWG AU



TE Part #1445856-1
STR RELIEF ASY,STRAIGHT SZ 11



TE Part #1-770986-0
MINI UMNL SOK 26-22AWG AU LP




TE Part #759025-000
7824E0422-9X




TE Part #1-770985-0
MINI UMNL PIN 26-22AWG AU LP



TE Part #1544210-2
CTS 2180 ETAME



TE Part #1445904-1
NUT,JAM,3/4-20,PKG QTY 100



TE Part #32861
TERMINAL,DG R 26-22 6



Documents

Product Drawings

RECPT,11-9,FLNG MT,STD KEY

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1445816-1_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1445816-1_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1445816-1_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773902-9_CPC_Catalog

English

1-1773902-9_CPC_Catalog

1-1773902-9_CPC_Catalog

German

1-1773902-9_CPC_Catalog

Japanese

AMP Circular Connectors for Commercial Signal & Power Applications Continued

English

Product Specifications

Application Specification

English