

SMA-A0204FTDX1K2

✓ ACTIVE

NEOHM | NEOHM SMA-A

TE Internal #: 5-2176315-1

1.2K ohm, Thin Film, Precision Resistor, 1 %, 0204, .4 W, ±50 ppm/° C, Metal Electrode Leadless Face (MELF), 2 Terminations, NEOHM SMA-A

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Element Type: **Thin Film**

Package Size Code: **0204**

Power Rating: **.4 W**

Resistance Value: **1.2K  $\Omega$**

Features

Product Type Features

|                   |                    |
|-------------------|--------------------|
| Resistor Type     | Precision Resistor |
| Element Type      | Thin Film          |
| Package Size Code | 0204               |

Configuration Features

|                     |   |
|---------------------|---|
| Number of Resistors | 1 |
|---------------------|---|

Electrical Characteristics

|                             |                           |
|-----------------------------|---------------------------|
| Operating Voltage           | 200 V                     |
| Power Rating                | .4 W                      |
| Resistance Value            | 1.2K $\Omega$             |
| Resistance Class            | 1k $\Omega$ – 1M $\Omega$ |
| Passive Component Tolerance | 1 %                       |

Termination Features

|                                         |                                      |
|-----------------------------------------|--------------------------------------|
| Surface Mount Resistor Termination Type | Metal Electrode Leadless Face (MELF) |
| Number of Terminations                  | 2                                    |



Dimensions

|                  |                 |
|------------------|-----------------|
| Product Diameter | 1.4 mm[.055 in] |
| Product Length   | 3.5 mm[.138 in] |

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 155 °C[-67 – 311 °F] |
| Temperature Coefficient     | ±50 ppm/°C                 |

Packaging Features

|                  |                |
|------------------|----------------|
| Packaging Method | Taped & Reeled |
|------------------|----------------|

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                              |
| Solder Process Capability                     | Reflow solder capable to 260°C                                                                                                |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

SMA-A0204FTDX1K2

1.2K ohm, Thin Film, Precision Resistor, 1 %, 0204, .4 W, ±50 ppm/°C, Metal Electrode Leadless Face (MELF), 2 Terminations, NEOHM SMA-A



TE Part # 2176316-5  
MELF SMA\_A 220R 0.1% 15PPM 0207 1W

TE Part # 6-2176314-9  
MELF SMA-A 10R 1% 50PPM 0102 0.3 W

TE Part # 3-2176315-2  
MELF SMA\_A 39K 0.1% 15PPM 0204 0.4W

TE Part # 9-2176316-4  
MELF SMA-A 330K 1% 50PPM 0207 1W

TE Part # 9-2176315-8  
MELF SMA-A 1M0 1% 50PPM 0204 0.4 W

Also in the Series | NEOHM SMA-A

Surface Mount Resistors(99)

Customers Also Bought

TE Part #294722-E  
STVQ/2 32 FI AB VV 7-03 TL \* \* 247 E 172

TE Part #3-1415379-1  
RT33LA24

TE Part #1-1462038-6  
IM06NS=IM RELAY 140mW 12V

TE Part #1473149-4  
SEMI-HARD TRAY ASSY DDR2 SODIMM 5.2H ST


TE Part #6-1625892-1  
3W SM M/OX 5% 5K6

TE Part #4-1879021-1  
SMW3 4R7 5%


TE Part #4-2176315-4  
MELF SMA\_A 330R 1% 50PPM 0204 0.4 W

TE Part #7-2176315-2  
MELF SMA\_A 68K 1% 50PPM 0204 0.4 W





TE Part #5530843-5  
CONN SEC II 25 POS 100C/L



TE Part #9-2176315-1  
MELF SMA-A 270K 1% 50PPM 0204 0.4 W

Documents

Product Drawings

MELF SMA\_A 1K2 1% 50PPM 0204 0.4W

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_5-2176315-1\_BA.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_5-2176315-1\_BA.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_5-2176315-1\_BA.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SMA-A-1017

English