



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: Hood

Cable Entry Location: Top

Hood & Base Locking Device Type: Side Clip

Sealable: Yes

Features

Product Type Features

Hood & Base Connector Product Type	Hood
Sealable	Yes

Body Features

Primary Product Color	Black
Cable Entry Location	Top

Mechanical Attachment

Hood & Base Locking Device Type	Side Clip
---------------------------------	-----------

Packaging Features

Packaging Method	Package
Packaging Quantity	72

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2120336-1
PROTECTION COVER


Also in the Series | MotorMan




Circular Connector Contact Inserts(2)



Connector Caps & Covers(2)



Connector Hardware(4)




Connector Seals & Cavity Plugs(2)



Connector Strain Relief(2)



Rectangular Connector Hoods & Bases (4)



Rectangular Contact Inserts(5)


Customers Also Bought




TE Part #1103427-2
HC26.Bu.4.C.5,2



TE Part #2120340-1
PLASTIC HOOD / KIT



TE Part #4-1601041-3
PC TAB STANDARD SIAMEZE



TE Part #6-1393048-5
RESOLVER V23401-U7018-B709

Documents

Product Drawings

HOOD KIT MOTORMAN HC 180 PLAST

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2120451-1_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2120451-1_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2120451-1_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Product Specification

English

Agency Approvals

CSA Certificate

English

