

Shunt release, up to 63A, 12-110V

Part no. **FAZ-XAA-NA12-110VAC**  
**102037**

<b>General specifications</b>		
Product name		Eaton Distribution parts
Part no.		FAZ-XAA-NA12-110VAC
EAN		4015081019281
Product Length/Depth		105 millimetre
Product height		75.5 millimetre
Product width		17.7 millimetre
Product weight		0.11 kilogram
Compliances		RoHS conform
Certifications		CE marking UL (File No. E257181) UL (Category Control Number DIHS, DIHS7) North America (UL listed, CSA certified) CSA (Class No. 1437-01) CSA-C22.2 No. 5-09 CSA (File No. 204453) UL 489 IEC/EN 60898 IEC 61373 EN45545-2
Product Tradename		None
Product Type		Distribution parts
Product Sub Type		None
Public Consumption		Yes
Product Family Description		ES-PMCC-PDC-Eaton Distribution parts
Globally Marketable		Yes
<b>Product Specification Details</b>		
Accessory/spare part type		Shunt release
Additional equipment required		Shunt release (for power circuit breaker)
Ambient operating temperature - max		40 °C
Ambient operating temperature - min		-5 °C
Application		Switchgear for 110-V systems
Assembly width		1
Degree of protection		UL/CSA Type: - IP20 (IEC) IP40
Device fitting		Miniature circuit breaker (MCB)
Enclosure width		105 mm
Frame		Standard front dimension: 45 mm
Frequency rating		50 Hz / 60 Hz
Functions		Shunt release (for power circuit breaker)
Mounting width		17.5 mm (1 space unit)
Number of contacts (change-over contacts)		0
Number of contacts (normally closed contacts)		1
Number of contacts (normally open contacts)		1
Number of poles at main contact unit - max		1
Number of switches (fault signal)		0
Rated operational voltage (Ue) - max		110 V
Rated switch current		0 A
Suitable for current of main contact unit - max		0 A
Terminal protection		Busbar tag shroud to BGV A3
Terminal type		Twin-purpose terminals
Type		Accessory Accessory for miniature circuit breaker

Used with			Shunt releases Accessory Accessory for miniature circuit breaker
Voltage range			12 V AC - 110 V AC
Voltage type			AC/DC

## Technical data ETIM 8.0

Devices for distribution board-/surface mounting (EG000062) / Auxiliary device for distribution board devices (EC001286)			
Electric engineering, automation, process control engineering / Electrical installation, device / Breaker switch component / Auxiliary contact unit for distribution board (ecI@ss10.0.1-27-14-35-02 [AKE327013])			
Device fitting			Miniature circuit breaker (MCB)
Additional equipment			Shunt release (for power circuit breaker)
Installed at the factory			No
Width in number of modular spacings			1
Number of contacts as normally open contact			1
Number of contacts as normally closed contact			1
Number of contacts as change-over contact			0
Number of fault-signal switches			0
Rated switch current		A	0
Rated voltage		V	110
Voltage type for actuating			AC/DC
With auto test for earth leakage function			No
Suitable for max. number of poles main contact unit (total)			1
Suitable for max. current main contact unit		A	0