

# WMS-2 HF 9,5 (EX16)RL YE - Shrink sleeve



0833245

<https://www.phoenixcontact.com/gb/products/0833245>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shrink sleeve, Roll, yellow, unlabeled, can be labeled with: THERMOMARK E.SLEEVE, THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLLMASTER 300/600, THERMOMARK ROLL X1, THERMOMARK ROLL, THERMOMARK ROLL 2.0, THERMOMARK W, THERMOMARK X1.2, cable diameter range: 4.8 ... 9.5 mm, unperforated, mounting type: slide-on, cable diameter range (automated processing): 4.8 ... 8 mm, Number of individual labels: 1, roll length: 80 m, text field height: 16 mm, text field width: 80000 mm

## Product description

The continuous shrink sleeves in the WMS-2 HF... product family, in size 3.2 ... 9.5, are suitable for automated processing with the THERMOMARK E.SLEEVE applicator. The continuous format of the material means that individual marker lengths can be realized. After the printing and applying process, you have the option of shrinking the marked shrink sleeves by applying heat manually and thus fixing them on the cable/wire.

## Your advantages

- Permanent and captive identification of single-core wires, wires, cables, pneumatic hoses, and other cylindrical objects
- High flexibility, as individual marker lengths ranging from 3.45 mm ... 2000 mm (0.14" ... 78.7") can be realized in combination with the cutter and perforation cutter
- As an option, the sleeves can be shrunk by applying heat manually to fix the sleeve in position
- High diameter coverage with a shrink ratio of 2:1
- Widely used and proven worldwide in the railway industry

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 0833245             |
| Packing unit                         | 1 pc                |
| Minimum order quantity               | 1 pc                |
| Sales key                            | BG2216              |
| Product key                          | BG2216              |
| Catalog page                         | Page 222 (C-3-2019) |
| GTIN                                 | 4055626309484       |
| Weight per piece (including packing) | 1,593.3 g           |
| Weight per piece (excluding packing) | 1,573 g             |
| Customs tariff number                | 39173200            |
| Country of origin                    | PL                  |

# WMS-2 HF 9,5 (EX16)RL YE - Shrink sleeve



0833245

<https://www.phoenixcontact.com/gb/products/0833245>

## Technical data

### Notes

|                      |                                                                                                                                                                                                                                                                                                                                     |
|----------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note on application  | For the THERMOMARK ROLL and THERMOMARK ROLL 2.0 roll printers, this material can only be processed with an external media hub.                                                                                                                                                                                                      |
| Material information | <p>The specified minimum wire diameter of the shrink sleeve refers to its use as a marking material and does not guarantee any insulation characteristics once shrunk.</p> <p>Depending on the processed material batch, as well as the storage and processing conditions, the maximum insertable wire diameter may be reduced.</p> |

### Product properties

|                     |                  |
|---------------------|------------------|
| Product type        | Shrink sleeve    |
| Area of application | Railway industry |
| Type                | Shrink sleeve    |

### Marking

|                             |                            |
|-----------------------------|----------------------------|
| Number of individual labels | 1                          |
| Identification technology   | Thermal transfer for rolls |

### Dimensions

|                |         |
|----------------|---------|
| Width          | 16 mm   |
| Length of roll | 80.00 m |

### External dimensions

|                  |                   |
|------------------|-------------------|
| Outside diameter | 4.8 mm ... 9.5 mm |
|------------------|-------------------|

### Text field

|                   |          |
|-------------------|----------|
| Text field width  | 80000 mm |
| Text field height | 16 mm    |

### Material specifications

|                                                        |                   |
|--------------------------------------------------------|-------------------|
| Color                                                  | yellow (RAL 1018) |
| Material                                               | Polyolefine       |
| Base element material                                  | polyolefine       |
| Shrink rate                                            | 2:1               |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3       |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3       |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3       |
| Components                                             | halogen-free      |
| Shrink temperature                                     | > 90 °C           |

### Cable/line

|                         |                   |
|-------------------------|-------------------|
| External cable diameter | 4.8 mm ... 9.5 mm |
|-------------------------|-------------------|

# WMS-2 HF 9,5 (EX16)RL YE - Shrink sleeve



0833245

<https://www.phoenixcontact.com/gb/products/0833245>

## Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

Test for substances that would hinder coating with paint or varnish

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

Scratch test for the determining scratch resistance

|               |                                |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements  | ≥ 5 N                          |
| Result        | Test passed                    |

Tesa film test

|               |                                     |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result        | Test passed                         |

UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result        | Test passed                           |
| Test duration | 96 h                                  |

Temperature resistance

|                        |                                 |
|------------------------|---------------------------------|
| Specification          | ANSI/UL 969-2018:03 (following) |
| Test duration          | 240 h                           |
| Rating 100 °C (121 °C) | Test passed                     |

Wipe resistance of inscriptions

|                                                   |                                                |
|---------------------------------------------------|------------------------------------------------|
| Specification                                     | DIN EN 61010-1 (VDE 0411-01):2020-03           |
|                                                   | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropyl<br>[CAS No. 67-63-0]                    | Test passed                                    |
| Water + Petroleum ether<br>[CAS No. 64742-82-1]   | Test passed                                    |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed                                    |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed                                    |
| Specification                                     | ISO 175:2010 (following)                       |
| Test duration                                     | 168 h                                          |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed                                    |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed                                    |
| Diesel<br>[CAS No. 68476-34-6]                    | Test passed                                    |
| IRM 901                                           | Test passed                                    |
| IRM 902                                           | Test passed                                    |

# WMS-2 HF 9,5 (EX16)RL YE - Shrink sleeve



0833245

<https://www.phoenixcontact.com/gb/products/0833245>

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                      |
|---------------|----------------------|
| Specification | EN ISO 22479:2022-06 |
| Result        | Test passed          |
| Procedure     | Method B             |
| Cycles        | 2                    |

## Salt spray test

|               |                           |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result        | Test passed               |
| Test duration | 96 h                      |

## Ambient conditions

|                                                     |                                                                                          |
|-----------------------------------------------------|------------------------------------------------------------------------------------------|
| Ambient temperature (operation)                     | -30 °C ... 105 °C                                                                        |
| Recommended ambient temperature (storage/transport) | 10 °C ... 25 °C                                                                          |
| Recommended humidity (storage/transport)            | 45 % ... 55 % (Storage in a dry and dark place in the original packaging is recommended) |
| Shelf life                                          | 2 years                                                                                  |

## Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Standards

|                       |            |
|-----------------------|------------|
| Standards/regulations | EN 45545-2 |
|-----------------------|------------|

## Mounting

|               |          |
|---------------|----------|
| Mounting type | slide-on |
|---------------|----------|

# WMS-2 HF 9,5 (EX16)RL YE - Shrink sleeve



0833245

<https://www.phoenixcontact.com/gb/products/0833245>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27281102 |
| ECLASS-12.0 | 27281102 |
| ECLASS-13.0 | 27281102 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001530 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# WMS-2 HF 9,5 (EX16)RL YE - Shrink sleeve



0833245

<https://www.phoenixcontact.com/gb/products/0833245>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)