

R75, Film, Metallized Polypropylene, Automotive Grade, 0.068 uF, 5%, 630 VDC, 85°C, Lead Spacing = 15mm



**Dimensions**

L	18mm +0.3mm
H	12mm +0.1mm
T	6mm +0.2mm
S	15mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

**Packaging Specifications**

<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	900

**General Information**

<b>Supplier:</b>	KEMET
<b>Series:</b>	R75
<b>Dielectric:</b>	Metallized Polypropylene
<b>Style:</b>	Radial
<b>Features:</b>	Automotive Grade, Pulse
<b>RoHS:</b>	Yes
<b>Lead:</b>	Wire Leads
<b>Qualifications:</b>	AEC-Q200
<b>AEC-Q200:</b>	Yes
<b>Miscellaneous:</b>	Above 85C DC And AC Voltage Derating Is 1.25%/C

**Specifications**

<b>Capacitance:</b>	0.068 uF
<b>Capacitance Tolerance:</b>	5%
<b>Voltage AC:</b>	250 VAC
<b>Voltage DC:</b>	630 VDC
<b>Temperature Range:</b>	-55/+105C
<b>Rated Temperature:</b>	85°C
<b>Dissipation Factor:</b>	0.04% 1kHz, 0.06% 10kHz, 0.25% 100kHz
<b>Insulation Resistance:</b>	100 GOhms
<b>Max dV/dt:</b>	1000 V/us
<b>Inductance:</b>	10 nH