



Brand of NTN Group

Technical data

UC206-19G2

Insert bearings



Spherical outer diameter, fixing by socket set screw, seal with slinger

VISUAL (S)



PRODUCT DEFINITION

| | |
|---|-----------|
| Brand | SNR |
| B - Width of Inner Ring | 38,1 mm |
| C - Width of Outer Ring | 19 mm |
| C1 - Distance center of OR to center of lubrication zone | 5 mm |
| d - Shaft diameter | 30,163 mm |
| D - Outer diameter of OR | 62 mm |
| G - Set screw size | 1/4-28UNF |
| m - Distance to set screw | 5,5 mm |



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

| | |
|---|----------|
| r - Radius Inner Ring | 0.6 |
| S - Distance front side/bearing centre | 15,9 mm |
| f0 - Factor | 13.7 |
| SW - Wrench size | 3,175 mm |

PRODUCT PERFORMANCE

| | |
|-----------------------------------|-------------|
| C - Dynamic load rating | 19500000 mN |
| C0 - Static load rating | 11200000 mN |
| Operating temperature min. | 253,15 °K |
| Operating temperature max. | 373,15 °K |

OTHER FEATURES

| | |
|--|---------|
| Mass | 0,31 kg |
| Recommended tightening torque for set screw | 3.7 N-m |

BEARING FREQUENCIES

| | |
|---|----------------------|
| BPFO - Over rolling frequency on outer ring (60 rpm) | 3.56820652173913 Hz |
| BPMF - Over rolling frequency on inner (60 rpm) | 5.43179347826087 Hz |
| BSF - Over rolling frequency on rolling element (60 rpm) | 4.62233110806801 Hz |
| BRF - Rotational frequency - rolling element (60 rpm) | 2.311165554034 Hz |
| FTF - Rotational frequency - cage (60 rpm) | 0.396467391304348 Hz |

