



Part Number : [1200910003](#)
Product Description : Nano-Change (M8)
Attachable Connectors, 90° Angle Female, 3
Poles
Series Number : 120091
Status : Active
Product Category : Circular Industrial
Connectors
Engineering Number : N03FA04124




Documents & Resources

Drawings
[1200910003_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per ED/88/2018 (15 January 2019)
EU RoHS	Compliant with Exemption 6(c); 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	120091
Description	Nano-Change (M8) Attachable Connectors, 90° Angle Female, 3 Poles
IP Rating	IP67
Product Name	Nano-Change (M8)
Type	Field Attachable Connector
UPC	78678832511

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC / 75V DC

Physical

Cable Diameter	3.50-5.00mm (.138-.197")
Coupling Type	Internal Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	None
Material - Connector Body	Nylon
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	9.071/g
Orientation	90° Angle
Poles	3
Temperature Range - Operating	0°C to +80°C

Wire Size (AWG)	N/A
-----------------	-----

This document was generated on Mar 27, 2025