

Thalassa PHD outdoor heavy duty - roof ventilation module H95 W1250 D420 - IP55

NSYPCVR124HD

EAN Code: 3606480680946

Price: 613,20 EUR

Main

Range	Thalassa	
Application	Outdoor heavy duty	
Accessory / separate part category	Enclosure accessory	
Product or component type	Ventilated roof	
Device application	Multi-purpose	
Mounting location	On top of enclosure	
Range compatibility	Thalassa Thalassa PHD suitable enclosure	
Quantity per set	Set of 1	

Complementary

Material	Steel with anti-corrosive coating	
Colour	Grey (RAL 7035)	
Surface finish	Polyester powder	
Fixing mode	By screws and claws (x3) - screw type M6 - roof fixing point location	
Corrosion resistance	90100 % conforming to ISO 12944 C4H	
Height	95 mm	
Width	1250 mm	
Depth	420 mm	
IP degree of protection	IP55 conforming to IEC 60529	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	127.500 cm
Package 1 Width	16.000 cm
Package 1 Length	13.000 cm
Package 1 Weight	12.448 kg
Unit Type of Package 2	P12
Number of Units in Package 2	5
Package 2 Height	80.000 cm
Package 2 Width	80.000 cm

Rates duty January 2016

Package 2 Length	120.000 cm
Package 2 Weight	73.000 kg



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

⊗ Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	1341ad4e-77b9-40e3-bab0-32043fbc5959

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No