

Features

- Independent Isolated Output
- 4.3 Inch LCD Display
- CC/CV operation mode
- Recovery Time: $\leq 100 \mu\text{s}$ (50 % load change, minimum load 0.5 A)
- Setting & Readback Resolution 10 mV / 2 mA
- Output ON/OFF
- OVP Protection
- Analog Control (Remote I/O) for Output ON / OFF
- Key Lock Function
- Smart cooling fan achieving low noise

RS PRO Tripple Output Linear D.C. Power Supply

RS Stock No.: 0760713,0760714,0760715,0760716,
0760717,0760719,0760720,0760721

MPN: RSPE-3323A



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The power supply unit features independent isolated output channels, enabling flexible multi-channel operation. Its digital panel control and 4.3-inch LCD display provide intuitive user interaction. With high-resolution settings and measurements down to 10 mV / 1 mA, it ensures precise voltage and current control.

It supports automatic series/parallel tracking and operates in both constant current (CC) and constant voltage (CV) modes. Safety is enhanced through multiple protection mechanisms, including overvoltage and overload protection. Additional functions include panel lock, output On/Off control, and a simple analog On/Off interface. Optimized heat dissipation ensures stable performance, making it ideal for demanding test environments.

General Specifications

Display	4.3" LCD
Power Source	AC 100 V / 120 V / 220 V $\pm$ 10 %, 230 V + 10 %/-6 %
Power Line Frequency	50 Hz or 60 Hz
Power Consumption	550 VA / 420 W, MAX
Dimensions	210 mm x 155 mm x 306 mm, (W x H x D)
Weight	Approx. 7 kg

Electrical Specifications

OUTPUT RATINGS	
CH1/CH2 Independent	0 V to 32 V / 0 A to 3 A
CH1/CH2 Series	0 V to 64 V / 0 A to 3 A
CH1/CH2 Parallel	0 V to 32 V / 0 A to 6 A
CH3	5 V, 5 A
VOLTAGE REGULATION	
Line	$\leq 0.01 \% + 3 \text{ mV}$
Load	$\leq 0.01 \% + 3 \text{ mV}$ (rating current $\leq 3 \text{ A}$)
	$\leq 0.02 \% + 5 \text{ mV}$ (rating current $> 3 \text{ A}$)
Ripple & Noise	$\leq 1 \text{ mVrms}$ (5 Hz to 1 MHz)
Recovery Time	$\leq 100 \mu\text{s}$ (50 % load change, minimum load 0.5 A)
Temperature Coefficient	$\leq 300 \text{ ppm}/^{\circ}\text{C}$

CURRENT REGULATION	
Line	$\leq 0.2 \% + 3 \text{ mA}$
Load	$\leq 0.2 \% + 3 \text{ mA}$
Ripple & Noise	$\leq 3 \text{ mArms}$
TRACKING OPERATION	
Tracking Error	$\leq 0.1 \% + 10 \text{ mV}$ of Master (No Load, with load add load regulation $\leq 100 \text{ mV}$)
Parallel Regulation	Line: $\leq 0.01 \% + 3 \text{ mV}$
	Load: $\leq 0.01 \% + 3 \text{ mV}$ (rating current $\leq 3 \text{ A}$)
	Load: $\leq 0.02 \% + 5 \text{ mV}$ (rating current $> 3 \text{ A}$)
Ripple & Noise	$\leq 1 \text{ mVrms}$ (5 Hz to 1 MHz)
Series Regulation	Line: $\leq 0.01 \% + 5 \text{ mV}$
	Load: $\leq 100 \text{ mV}$
Ripple & Noise	$\leq 2 \text{ mVrms}$ (5 Hz to 1 MHz)
OVP	
Range	CH1/CH2: OFF, ON (1 V to 36 V)
Resolution	1 V
Accuracy	$\leq \pm 1 \text{ V}$
DISPLAY	
LCD	4.3-inch single color LCD display
Ammeter	CH1/CH2: 3.200 A, full scale, 4 digits or 3 digits
Current Resolution	1 mA or 10 mA
Voltmeter	CH1/CH2: 32.00 V, full scale, 4 digits or 3 digits
Voltage Resolution	10 mV or 100 mV
ACCURACY	
Setting/Readback Accuracy	Voltage: $\pm (0.1 \% \text{ of reading} + 30 \text{ mV})$ (4 digits) $\pm (0.1 \% \text{ of reading} + 200 \text{ mV})$ (3 digits)
	Current: $\pm (0.3 \% \text{ of reading} + 6 \text{ mA})$ (4 digits) $\pm (0.3 \% \text{ of reading} + 20 \text{ mA})$ (3 digits)
CH3 ON THE GPE-3323A	
Output	5 V $\pm 5 \%$, 5 A
Line	$\leq 3 \text{ mV}$
Load	$\leq 5 \text{ mV}$
Ripple & Noise	$\leq 1 \text{ mVrms}$ (5 Hz to 1 MHz)
OVP	5.5 V
INSULATION	
Chassis and Terminal	20 M Ω or above (DC 500 V)
Chassis and AC cord	30 M Ω or above (DC 500 V)
OPERATION ENVIRONMENT	
Indoor Use, Altitude: $\leq 2000 \text{ m}$	
Ambient Temperature: 0 °C to 40 °C	
Relative Humidity: $\leq 80 \%$	
Installation Category: II; Pollution Degree: 2	
STORAGE ENVIRONMENT	
Ambient Temperature: -10 °C to 70 °C	
Relative Humidity: $\leq 70 \%$	

Approvals

Directive: EMC; LVD; WEEE; RoHS

The product is in conformity with the following standards or other normative documents:

© EMC	
EN 61326-1 :	Electrical equipment for measurement, control and laboratory use -- EMC requirements
Conducted & Radiated Emission EN 55011 / EN 55032	Electrical Fast Transients EN 61000-4-4
Current Harmonics EN 61000-3-2 / EN 61000-3-12	Surge Immunity EN 61000-4-5
Voltage Fluctuations EN 61000-3-3 / EN 61000-3-11	Conducted Susceptibility EN 61000-4-6
Electrostatic Discharge EN 61000-4-2	Power Frequency Magnetic Field EN 61000-4-8
Radiated Immunity EN 61000-4-3	Voltage Dip/ Interruption EN 61000-4-11 / EN 61000-4-34
© Safety	
EN 61010-1 :	Safety requirements for electrical equipment for measurement, control, and laboratory use - Part 1: General requirements

Similar Products

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3
	RS PRO	RSPE-1326A			
	RS PRO	RSPE-2323A			
	RS PRO	RSPE-4323A			

Order Information

RSPE-3323A 3 Channel 217 W Linear DC Power Supply

Included Accessories

Power cord x 2 (UK & VDE Types)

RSPE-3323A Test lead GTL-104 x 3

Mechanical Specifications

