

**Safety data sheet
according to UK REACH**

Printing date 23.01.2026

Version number 5 (replaces version 4)

Revision: 16.06.2025

SECTION 1: Identification of the substance/mixture and of the company/undertaking**· 1.1 Product identifier****· Trade name:** Stone and facade cleaner 3-in-1 RM 611**· 1.2 Relevant identified uses of the substance or mixture and uses advised against**

No further relevant information available.

· Application of the substance / the mixture High pressure cleaner**· 1.3 Details of the supplier of the safety data sheet****· Manufacturer/Supplier:****Alfred Kärcher SE & Co. KG**

Alfred-Kärcher-Str. 28-40

D - 71364 Winnenden

Tel.: +49-7195-14-0

Kärcher (UK) Ltd.

Kärcher House

Brookhill Way

Banbury

Oxon OX16 3ED

Great Britain

Tel.: +44-1295-752-000

Internet: www.karcher.com**· Further information obtainable from:**

Regulatory Affairs

Tel.: +49-7195-14-0

productsafety.management.de@karcher.com**· 1.4 Emergency telephone number:**

For Hazardous Materials [or Dangerous Goods] Incidents

Spill, Leak, Fire, Exposure, or Accident

Call CHEMTREC Day or Night

Within USA and Canada: 1-800-424-9300

Outside USA and Canada: +1-703-527-3887 (collect calls accepted)

SECTION 2: Hazards identification**· 2.1 Classification of the substance or mixture****· Classification according to Regulation (EC) No 1272/2008**

The product is not classified, according to the GB CLP regulation.

· 2.2 Label elements**· Labelling according to Regulation (EC) No 1272/2008** Void**· Hazard pictograms** Void**· Signal word** Void

(Contd. on page 2)

Safety data sheet according to UK REACH

Printing date 23.01.2026

Version number 5 (replaces version 4)

Revision: 16.06.2025

Trade name: Stone and facade cleaner 3-in-1 RM 611

Hazard statements Void

(Contd. of page 1)

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Description: Mixture of substances listed below with non-hazardous additions.

Dangerous components:

CAS: 68515-73-1	alkyl polyglucoside	1-5%
NLP: 500-220-1	Eye Dam. 1, H318	
Reg.nr.: 01-2119488530-36	Specific concentration limit: Eye Dam. 1; H318: C ≥ 10 %	

Additional information For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

4.1 Description of first aid measures

After inhalation Supply fresh air; consult doctor in case of complaints.

After skin contact Generally the product does not irritate the skin.

After eye contact Rinse opened eye for several minutes under running water.

After swallowing

Rinse out mouth and then drink plenty of water.

If symptoms persist consult doctor.

4.2 Most important symptoms and effects, both acute and delayed No further relevant information available.

4.3 Indication of any immediate medical attention and special treatment needed

No further relevant information available.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing agents

CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

5.2 Special hazards arising from the substance or mixture No further relevant information available.

5.3 Advice for firefighters

Protective equipment: No special measures required.

Additional information Collect contaminated fire fighting water separately. It must not enter the sewage system.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures Not required

(Contd. on page 3)

**Safety data sheet
according to UK REACH**

Printing date 23.01.2026

Version number 5 (replaces version 4)

Revision: 16.06.2025

Trade name: Stone and facade cleaner 3-in-1 RM 611

(Contd. of page 2)

· 6.2 Environmental precautions:

- Dilute with plenty of water.
- Do not allow to enter sewers/ surface or ground water.
- Do not allow to penetrate the ground/soil.

· 6.3 Methods and material for containment and cleaning up:

- Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders).

· 6.4 Reference to other sections

- See Section 7 for information on safe handling
- See Section 8 for information on personal protection equipment.
- See Section 13 for disposal information.

SECTION 7: Handling and storage

- 7.1 Precautions for safe handling** No special precautions are necessary if used correctly.
- Information about fire - and explosion protection:** No special measures required.
- 7.2 Conditions for safe storage, including any incompatibilities**
- Storage**
- Requirements to be met by storerooms and receptacles:** No special requirements.
- Information about storage in one common storage facility:** Keep away from food, beverages and feed.
- Further information about storage conditions:** None.
- 7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- 8.1 Control parameters**
- Ingredients with limit values that require monitoring at the workplace:**
The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.
- 8.2 Exposure controls**
- Appropriate engineering controls** No further data; see section 7.
- Individual protection measures, such as personal protective equipment**
- General protective and hygienic measures** Wash hands before breaks and at the end of work.
- Respiratory protection:** Not necessary if room is well-ventilated.
- Hand protection** Not required
- Material of gloves** Not required
- Penetration time of glove material** Not required
- Eye/face protection** Not required

GB

(Contd. on page 4)

Safety data sheet according to UK REACH

Printing date 23.01.2026

Version number 5 (replaces version 4)

Revision: 16.06.2025

Trade name: Stone and facade cleaner 3-in-1 RM 611

(Contd. of page 3)

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

General Information

Physical state	Liquid
Colour:	Whitish
Odour:	flowery
Odour threshold:	Not determined
Melting point/freezing point:	0 °C
Boiling point or initial boiling point and boiling range	undetermined
Flammability	Not applicable
Lower and upper explosion limit	
Lower:	Not determined
Upper:	Not determined
Flash point:	Not applicable
Auto-ignition temperature:	not applicable
Decomposition temperature:	Not determined
pH at 20 °C	6-8
pH-value 1 %:	6-8
Viscosity:	
Kinematic viscosity	Not determined
dynamic at 20 °C:	1916 mPas
Solubility	
Water:	Fully miscible
Partition coefficient n-octanol/water (log value)	Not determined
Vapour pressure:	Not determined
Density and/or relative density	
Density at 20 °C:	1.011 g/cm ³
Relative density	Not determined
Vapour density	Not determined
Relative gas density	Not determined

9.2 Other information

Appearance:	
Form:	Fluid
Important information on protection of health and environment, and on safety.	
Ignition temperature:	Product is not selfigniting.
Explosive properties:	Product does not present an explosion hazard.
Change in condition	
Evaporation rate	Not determined

Information with regard to physical hazard classes

Explosives	Void
Flammable gases	Void
Aerosols	Void
Oxidising gases	Void
Gases under pressure	Void
Flammable liquids	Void

(Contd. on page 5)

Safety data sheet according to UK REACH

Printing date 23.01.2026

Version number 5 (replaces version 4)

Revision: 16.06.2025

Trade name: Stone and facade cleaner 3-in-1 RM 611

(Contd. of page 4)

· Flammable solids	Void
· Self-reactive substances and mixtures	Void
· Pyrophoric liquids	Void
· Pyrophoric solids	Void
· Self-heating substances and mixtures	Void
· Substances and mixtures, which emit flammable gases in contact with water	Void
· Oxidising liquids	Void
· Oxidising solids	Void
· Organic peroxides	Void
· Corrosive to metals	Void
· Desensitised explosives	Void

SECTION 10: Stability and reactivity

- **10.1 Reactivity** corresponds to 10.3
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known

SECTION 11: Toxicological information

- **11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008**
- **Acute toxicity** Based on available data, the classification criteria are not met.

· **LD/LC50 values relevant for classification:**
3811-73-2 sodium pyrithione

Oral LD50 500 mg/kg (ATE)

Dermal LD50 790 mg/kg (ATE)

- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.

(Contd. on page 6)

Safety data sheet according to UK REACH

Printing date 23.01.2026

Version number 5 (replaces version 4)

Revision: 16.06.2025

Trade name: Stone and facade cleaner 3-in-1 RM 611

(Contd. of page 5)

· **Aspiration hazard** Based on available data, the classification criteria are not met.

· **11.2 Information on other hazards**

· **Endocrine disrupting properties**

1222-05-5 | 1,3,4,6,7,8-hexahydro-4,6,6,7,8,8-hexamethylindeno[5,6-c]pyran

List II

SECTION 12: Ecological information

· **12.1 Toxicity**

· **Aquatic toxicity:**
68515-73-1 alkyl polyglucoside

LC50/96 h | 126 mg/l (fish)

EC50/48 h | >100 mg/l (Daphnia magna)

3811-73-2 sodium pyrithione

LC50/96 h | 0.00767 mg/l (Danio rerio) (OECD 203)

EC50/48 h | 0.022 mg/l (Daphnia magna) (OECD 202)

EC50/72 h | 0.46 mg/l (F29) (OECD 201)

NOEC | 0.08 mg/l // 72 h (F29) (OECD 201)

· **12.2 Persistence and degradability** No further relevant information available.

· **12.3 Bioaccumulative potential** No further relevant information available.

· **12.4 Mobility in soil** No further relevant information available.

· **12.5 Results of PBT and vPvB assessment**

· **PBT:** Not applicable

· **vPvB:** Not applicable

· **12.6 Endocrine disrupting properties** For information on endocrine disrupting properties see section 11.

· **12.7 Other adverse effects**

· **Additional ecological information:**

· **COD-value:** 85.000 mg/l

· **General notes:**

The surfactant(s) contained in this preparation complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.

The product does not contain organic complexing agents.

The product does not contain organically bounded halogens (AOX-free).

Do not allow product to reach ground water, water course or sewage system.

(Contd. on page 7)

GB

Safety data sheet
according to UK REACH

Printing date 23.01.2026 Version number 5 (replaces version 4) Revision: 16.06.2025

Trade name: Stone and facade cleaner 3-in-1 RM 611

(Contd. of page 6)

Danger to drinking water if even small quantities leak into the ground.

SECTION 13: Disposal considerations

- 13.1 Waste treatment methods
- Recommendation
Must not be disposed together with household garbage. Do not allow product to reach sewage system.
Must be specially treated adhering to official regulations.
- European waste catalogue
20 01 30 | detergents other than those mentioned in 20 01 29
- Uncleaned packaging:
- Recommendation:
Empty contaminated packagings thoroughly. They may be recycled after thorough and proper cleaning.
- Recommended cleansing agents: Water, if necessary together with cleaning agents.

SECTION 14: Transport information

- | | |
|--|----------------|
| 14.1 UN number or ID number | |
| ADR, IMDG, IATA | Void |
| 14.2 UN proper shipping name | |
| ADR, IMDG, IATA | Void |
| 14.3 Transport hazard class(es) | |
| ADR, ADN, IMDG, IATA | |
| Class | Void |
| 14.4 Packing group | |
| ADR, IMDG, IATA | Void |
| 14.5 Environmental hazards: | Not applicable |
| 14.6 Special precautions for user | Not applicable |
| 14.7 Maritime transport in bulk according to IMO instruments | Not applicable |
| UN "Model Regulation": | Void |

Safety data sheet according to UK REACH

Printing date 23.01.2026

Version number 5 (replaces version 4)

Revision: 16.06.2025

Trade name: Stone and facade cleaner 3-in-1 RM 611

(Contd. of page 7)

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Poisons Act

Regulated explosives precursors

None of the ingredients is listed.

Regulated poisons

None of the ingredients is listed.

Reportable explosives precursors

None of the ingredients is listed.

Reportable poisons

1310-73-2	sodium hydroxide	12% of total caustic alkalinity
1310-58-3	potassium hydroxide	17% of total caustic alkalinity

Directive 2012/18/EU

Named dangerous substances - ANNEX I None of the ingredients is listed.

National regulations

Information about limitation of use: Employment restrictions concerning juveniles must be observed.

15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.
A product information sheet can be provided if requested.

Relevant phrases

H318 Causes serious eye damage.

Contact:

Regulatory Affairs

Tel.: +49-7195-14-0

productsafety.management.de@karcher.com

Abbreviations and acronyms:

ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

Eye Dam. 1: Serious eye damage/eye irritation – Category 1

(Contd. on page 9)

Safety data sheet
according to UK REACH

Printing date 23.01.2026

Version number 5 (replaces version 4)

Revision: 16.06.2025

Trade name: Stone and facade cleaner 3-in-1 RM 611

· * **Data compared to the previous version altered.**

(Contd. of page 8)

· 0·011-284·0 RM 611/10 2·833