








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		REVISED PER ECN-25-302515	17JAN2025	TR	RCG



Note:
 X= 1,2,3,4,5,6
 YYWWD
 YY=YEAR
 WW=WEEK
 D=1 for Sunday -
 7 for Saturday



NOTE:
 1.Housing:PA46 BLACK UL94V-0.(RoHS)
 2.Insert: PBT BLACK UL94V-0.(RoHS)
 3.Shielding:Copper Alloy with Nickel Plated.(RoHS)
 4.Contact:T0.35*0.46mm Phosphor Bronze(RoHS).
 5.Led:YELLOW(RoHS)
 6.Led:GREEN(RoHS)
 ※Mates With Modular Plug Conforming To Fcc Part 68,Subpart F.
 ※The Dimensions Marked"▲" Symbols Are Stand For Key Characteristics.



GF	2496704-6
0.0762 μm [3μ"]	2496704-5
0.1524 μm [6μ"]	2496704-4
0.381 μm [15μ"]	2496704-3
0.762 μm [30μ"]	2496704-2
1.27 μm [50μ"]	2496704-1
GOLD PLATING THICKNESS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TARUN, R	10NOV2024	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK	RAMESH, KIVADER	11NOV2024	RJ45 W/O MAGNET 2X1 LED		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	RAGHAVAN, CG	11NOV2024	NAME		
0 PLC	± -	PRODUCT SPEC		108-161621			
1 PLC	± 0.35	APPLICATION SPEC		114-161218			
2 PLC	± 0.25	SIZE	A2	CAGE CODE	00779	DRAWING NO	C=2496704
3 PLC	± 0.15	WEIGHT	-	RESTRICTED TO	-		
4 PLC	± -	CUSTOMER DRAWING		SCALE	1:1	SHEET	1 OF 2
ANGLES	± 2°			REV	A		
MATERIAL	-						
FINISH	-						