

Product data sheet

Specifications



Repacked, miniature circuit breaker (MCB), Acti9 C60PV-DC, 2P, 16A, B curve, 1.5kA (IEC/EN 60947-2)

A9N61651W



This repacked option saves 4.771 over the standard condition

Main

Range of product	C60
Product or component type	Miniature circuit-breaker
Device short name	C60PV-DC
Poles description	2P
Number of protected poles	2
Network type	DC
Curve code	B
Utilisation category	Category A conforming to EN/IEC 60947-2
Suitability for isolation	Yes conforming to EN/IEC 60947-2

Complementary

[In] rated current	16 A
Voltage Drop	648 mV 40.5 mOhm 10.4 W 16 A
[Ue] rated operational voltage	800 V DC
Magnetic tripping limit	5.5 x In
Breaking capacity	3 kA Icu at 650 V DC 1.5 kA Icu at 800 V DC
[Ics] rated service breaking capacity	1.5 kA 100 % - 800 V DC 3 kA 100 % - 650 V DC
[Ui] rated insulation voltage	1000 V DC
[Uimp] rated impulse withstand voltage	6 kV
Polarity sensitivity	No (can protect against bi-directional current)
Contact position indicator	Yes
Control type	Toggle
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	8
Height	132.7 mm
Width	72 mm
Depth	77.4 mm
Product weight	0.545 kg
Colour	White

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mechanical durability	20000 cycles
Electrical durability	1500 cycles L/R = 2 ms
Locking options description	Padlocking in OFF position
Connections - terminals	Tunnel terminal (downside) 1...25 mm² rigid Tunnel terminal (downside) 1...16 mm² flexible Pre-wired cable (upside)
Wire stripping length	14 mm
Tightening torque	2.5 N.m
Market segment	Residential Small commercial
Compatibility code	C60PV-DC

Environment

Standards	EN/IEC 60947-2
Pollution degree	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 cm
Package 1 Width	7.5 cm
Package 1 Length	13.6 cm
Package 1 Weight	524.5 g
Unit Type of Package 2	S03
Number of Units in Package 2	30
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	16.498 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	240
Package 3 Height	15 cm
Package 3 Width	80 cm
Package 3 Length	60 cm
Package 3 Weight	2493.92 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

5 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

C839c050-8547-41ce-b0db-e9813554fc09

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins