

Description

STAINLESS STEEL TOP PLATE CASTOR, RED POLYURETHANE 200MM

Fixed

KF5BA200-28L

Part Number

Swivel


KP5BA200-28L

Swivel and brake

KP5BD200-28L



	Fixed	Swivel	Swivel+brake
Wheel Diameter ØD	200 mm		
Overall Height H	240 mm ±1		
Size of plate A X B	129 x 106 mm±1		
Plate hole centres a x b	105 x 80 mm±0,3		
Plate hole	11 mm		
Offset F ±1	\	48 mm	48 mm
Width of Tread	50 mm±0,5		
Hardness of tread	shore A ± 98		
Load capacity	300 Kg		
Weight	1,7 kg	1,9 kg	2,5 kg
Temperature	- 20 / + 60 °C		



Castor Assembly :

Pressed stainless steel -AISI 304-. Swivel on two rows of balls.
Fastening by top plate.
Total lock. Metal pedal.

Wheel :

Wheel centre made of White Polyamide.
Tread : Red injected Polyurethane non marking.
Hub : Plain bore.

Features :

Low starting effort. High load capacity.
Lightweight, highly resistant to knocks and other impacts, abrasion as well as a great many chemical substances.
Corrosion resistant, easy to clean. Specially designed for humid environments.
Suited for Food industry, Hospital or Industrial Kitchen equipment.
Non staining red tyre.
Medium duty.