

ABSA lacing cord in wax impregnated polyamide




ABSA



ABSA nylon lacing cords are formed as a slightly rounded mass of continuous filaments which flatten, form a tight knot and will not penetrate insulations. Use of this type of cord eliminates the inconvenience and gers of cuts and weals to operators' fingers usually experienced with the round mono-filament type cords.

- Material :** Continuous filaments
6 denier impregnated with 30 to 35% wax.
- Colour :** Natural
- Elongation at break :** 10 to 40 %
- Melting point :** 76 - 84 (ASTM D 127)
- Chemical resistance :** Good resistance to micro-organisms, ozone and ageing.



type	article number	 bobbin	length per bobbin (m)	width x thickness cord (mm)	tensile strength (daN)	denier
Small bobbins - natural						
ABSA 2/840 PB	0643 0060 001	18	66	1,1 x 0,3	13	1880
ABSA 3/840 PB	0643 0061 001	18	45	1,2 x 0,4	19	2800
ABSA 4/840 PB	0643 0062 001	18	33	1,3 x 0,5	26	3700
ABSA 6/840 PB	0643 0063 001	18	22	1,4 x 0,6	39	5600
Standard bobbins - natural						
ABSA 2/840 B	0643 0001 001	12	200	1,1 x 0,3	13	1880
ABSA 3/840 B	0643 0002 001	12	200	1,2 x 0,4	19	2800
ABSA 4/840 B	0643 0003 001	12	200	1,3 x 0,5	26	3700
ABSA 6/840 B	0643 0004 001	6	200	1,4 x 0,6	39	5600
Large bobbins - natural						
ABSA 2/840 RB	0643 0030 001	12	500	1,1 x 0,3	13	1880
ABSA 3/840 RB	0643 0031 001	6	500	1,2 x 0,4	19	2800
ABSA 4/840 RB	0643 0032 001	6	500	1,3 x 0,5	26	3700

