



Z-PACK | Z-PACK 2mm HM

TE Internal #: 5319919-5


TE Internal Description: 2MM 56 POS, HEADER

Hard Metric Male Connector: Traditional Backplane, Mezzanine, 2mm

[View on TE.com >](#)

Connectors > PCB Connectors > Backplane Connectors > Hard Metric Backplane Connectors >

Hard Metric Male Connector: Traditional Backplane, Mezzanine, 2mm



PCB Connector Type: **PCB Mount Header**

Data Rate: **≤1 Gb/s**

Number of Columns: **6**

Number of Rows: **8**

Backplane Architecture: **Mezzanine**

[All Hard Metric Male Connector: Traditional Backplane, Mezzanine, 2mm \(124\)](#)

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Ground Feature Type	Grounding Contact
Backplane Interface Type	2mm HM
Connector System	Board-to-Board
PCB Connector Type	PCB Mount Header
Sealable	No

Configuration Features

Number of Columns	6
Number of Rows	8
Backplane Architecture	Mezzanine
Number of Positions	56
PCB Mount Orientation	Vertical

Signal Characteristics

Data Rate	≤1 Gb/s
-----------	---------

Body Features

Primary Product Color	Black
-----------------------	-------



Contact Features

Contact Underplating Material	Nickel
Contact Base Material	Phosphor Bronze
CompactPCI Designation	None
PCB Contact Termination Area Plating Material	Tin
Feedthrough Post Length	3.7 mm
Contact Type	Pin
Contact Mating Area Plating Material	Gold (Au)
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Contact Current Rating (Max)	.7 A

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
---------------------------	--------------------------

Mechanical Attachment

Connector Mounting Type	Board Mount
Mating Alignment Type	Polarizing Peg

Housing Features

Housing Material	Polyester - GF
Centerline (Pitch)	2 mm[.078 in]

Dimensions

Backplane Module Length	15.88 mm
-------------------------	----------

Operation/Application

Shielded	No
Circuit Application	Power & Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tube
------------------	------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------




EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2019 (201) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Also in the Series | Z-PACK 2mm HM




Board-to-Board Headers & Receptacles(46)




Connector Contacts(2)




Connector Hardware(91)



Hard Metric Backplane Connectors (266)



Power Contacts(2)



Rectangular Power Connectors(46)

Customers Also Bought



TE Part #6368296-1
ASSY,SHLD,2X8,STK MJ,WAVE PNL



TE Part #4-1879269-9
RP 2A 32R4 0.1% 15PPM CUT LENGTH



TE Part #3-338088-3
8/8 INV.MOD.JACK LOW HALOGEN



TE Part #6116353-8
INV MJ,1X2,PNL GRD,LED (YG/YG)



TE Part #6-147723-9
20 MODIV VRT SR SFMNT 30AU




TE Part #5746443-1
A/L UNIV HDR 10P ACT PIN LAT



TE Part #3-1393789-9
V23079A2011B301



TE Part #84534-6
1.25MM FFC POST PLATED V 6P



TE Part #7-1571986-2
A101J1AV2Q004AM marking O -



TE Part #1241164-5
2X 5P MOD2A-P STLEI

Documents

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_5319919-5_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_5319919-5_A.3d_igs.zip

English

Customer View Model

ENG_CVM_5319919-5_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English