



# A POWERFULL TABLET READY FOR HOSTILE ENVIRONMENTS

Slim, easy to carry around and extremely rugged. The Fieldbook-N80 is IP 67 (immersion proof). While most IP67 devices in its category have an embedded battery pack, the FIELDBOOK N80 has a removable one. Thanks to the double lock system and gasket in the trap door the battery compartment of the N80 remains fully sealed preventing liquids to run into the device. Its light weight and slim form factor make it easy to carry around. A hand strap greatly ease the user in his daily tasks. The performances and ruggedness of the FIELDBOOK N80 tablet as well as its sunlight readable screen make it the ideal tool for indoor and outdoor use.

# **FIELDBOOK N80**

# Rugged 8" tablet with removable battery pack

- ✓ IP67 water, drop and dust resistant
- ✓ Powerful Qualcomm MSM8940 Snapdragon 435 CPU
- √ 3GB RAM / 32GB internal storage
- ✓ 3G/4G, Wifi(a/b/g/n/ac), BT4.1, GPS (PIFA), NFC Windows 10 Pro
- ✓ 8" / 1280x800 IPS / 450 nits/ 10 points multi touch / Outdoor readable

IP67
WATER, DUST, DROP
PROOF

REMOVABLE
BATTERY PACK



LOGIC INSTRUMENT an ARCHOS company

www.logic-instrument.com

#### **OPERATING SYSTEM**

Android 8.1 Oreo

#### **PERFORMANCE**

Qualcomm MSM8940 – Snapdragon 435 Octa-Core ARM Cortex A53 Up to 1.4 GHz 3GB RAM + 32 GB Storage

#### **SCREEN**

8 inch

Resolution 800x1280swx

IPS technology Multi touch 10pts - Works with gloves

Outdoor readable: 450 nits Tempered Glass

#### CONNECTIVITY

Wifi 802.11 a/b/g/n/ac; 2.4 GHz/5GHz

Bluetooth 4.1

GSM: 850/900/1800/1900

EVDO: BC0

WCDMA: B1/B2/B5/B8 TD-SCDMA: B34/B39

TDD-LTE: B38/B39/B40/B41

FDD-LTE: B1/B3/B4/B5/B7/B8/B17/B20/B28

NFC (HF) 13.56MHz, ISO 14443AB, 15693, 18092, MIFARE

Ublox M8N GPS, Glonass

#### **INTERFACES**

1 x USB type-C port

1 x micro SD slot

2 x nano SIM card slots

1 x external GPS antenna connector (PIFA)

2 x function buttons (F1,F2), Power ON/OFF, Volume+/-

POGO interface connector







Removable battery pack

#### CAMERAS POWER

Front camera : 5MP

Back camera: 16MP Sony with Flash LED

### **SENSORS**

G-Sensor/Gyroscope/Light Sensor/E-compass

# **POWER SUPPLY**

Charger: USB Type-C 5V/2A Battery: 8,000mAh/3.7v –removable-Compatible Quick Charge 3.0

## **DIMENSIONS / WEIGHT**

235 x 146 x 13 mm - 560g

## **OPERATOR /NETWORKS**

GSM: 850/900/1800/1900

#### **RESISTANCE**

IP67 (water and dust resistant)
1.2m drop resistant
Operating temp. -20°C to +60°C

Operating temp. -20°C to +60° Storage temp. -30°C to +70°C

#### **OPTIONS & ACCESSORIES**

Protection film
Vehicle dock
Car adapter
Battery charger
LAN module
UHF RFID module
1D/2D barcode scanner
Spare battery



www.logic-instrument.com

Logic instrument UK +44 (0)11 89 77 24 60 jratcliffe@logic-instrument.com Logic instrument France +33 (0)1 69 33 10 80 bienvenue@logic-instrument.com Logic instrument Germany +49 (0)61 04 94 59 93 willkommen@logic-instrument.com Logic instrument Benelux +31 (0)653 647 107 kubinek@archos.com