



Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Ferrule**

Packaging Method: **Bag**

Packaging Quantity: **100**

Features

Product Type Features

Strain Relief Accessory Type	Ferrule
------------------------------	---------

Housing Features

Body Orientation	Horizontal
------------------	------------

Dimensions

	.625 in
--	---------

Packaging Features

Packaging Method	Bag
Packaging Quantity	100

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 543344-1
SAHT FERR ON AMPLIMITE FRAME W /O DIES

Also in the Series | AMPLIMITE Kit

Connector Caps & Covers(2)

Connector Hardware(91)

Connector Seals & Cavity Plugs(4)

Connector Strain Relief(126)


Customers Also Bought

TE Part #1658655-1
KIT,HDP-20,ENCLSUR,PLUG,SIZE 1


TE Part #CAT-T3437-ST2999
STD Snap-On Markers

TE Part #357197-000
202K121-100/86-0

TE Part #5-104506-5
MTE PIN LP



TE Part #5069802018
CGPT-1.6/0.8-0-STK



TE Part #NB15734001
RNF-150-1/8-0-SP

Documents

Product Drawings

SHLDING FERRULE,PLTD TIN,BULK

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-747580-1_V.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-747580-1_V.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-747580-1_V.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - Cable Connectors

English

AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG

English

Product Specifications

Application Specification

English

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)



English

[Shielding Hardware Kits with AMPLIMITE HD-20 Solder Contact Connectors](#)

English

[Instruction Sheet \(U.S.\)](#)

English