



**Part Number :** [643193218](#)

**Product Description :** .635mm, 1.50mm, CMC Receptacle, 32 Circuits, Right Wire Output, Gray Coding, Mat Sealed

**Series Number :** 64319

**Status :** Active

**Product Category :** Connector Housings

---



## Documents & Resources

### Drawings

[643193218\\_sd.pdf](#)

### 3D Models and Design Files

[643193218\\_stp.zip](#)

### Specifications

[AS-64319-002-001.pdf](#)

[AS-64319-002-CH-001.pdf](#)

[AS-64319-002-FR-001.pdf](#)

[AS-64319-002-SP-001.pdf](#)

[984200002-AS-KR-000.pdf](#)

[AS-98420-002-001.pdf](#)

[AS-98420-002-CH-001.pdf](#)

[AS-98420-002-FR-001.pdf](#)

[AS-98420-002-SP-001.pdf](#)

[PK-64319-001-001.pdf](#)

[PS-64319-001-001.pdf](#)

[PS-64319-002-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant
China RoHS	 per SJ/T 11365-2006

EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Dodecamethylcyclohexasiloxane; Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Connector Housings
Series	64319
Description	.635mm, 1.50mm, CMC Receptacle, 32 Circuits, Right Wire Output, Gray Coding, Mat Sealed
Application	Automotive, Power, Wire-to-Board
Comments	Current tested on a 5 terminals loaded connector, current for temperature increase of 40°C; Current max = 6.0A for 0.635mm Terminal (0.75mm <sup>2</sup> wire) and 12.0A

	for 1.50mm Terminal (2.00mm <sup>2</sup> wire)
More Detailed Tech Information	Sealed, high-density, modular connecting system for Power Train and Body Electronics applications in cars, trucks, busses
Product Name	CMC
UPC	883906134853

## Physical

Circuits Detail	8 x 1.5mm & 24 x 0.635mm terminals
Circuits (maximum)	32
Color - Resin	Gray
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	29.426/g
Number of Rows	4
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	2.54mm, 3.70mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

## Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

## Mates With / Use With

### Use with Part(s)

Description	Part Number
CMC Wire Cap for 32 Circuits, CMC Receptacle Mat Sealed	<u>643191201</u>

CMC 0.635mm Blind Cavity Plug	<u>643251010</u>
CMC 1.50mm Blind Cavity Plug	<u>643251023</u>
0.635mm CMC CP Female Terminals	<u>64322</u>
1.50mm CMC CP Female Terminals	<u>64323</u>

---

## Application Tooling

### Global

Description	Part Number
Continuity Test Pen Assembly	<u>638121100</u>
Unlocking Tool for CMC and CMX Receptacle Connector	<u>638241200</u>