

# PRODUCT DATASHEET

## FLOODLIGHT 180 W 3000 K IP65 BK

**FLOODLIGHT 180 | Floodlight with symmetrical light output with 180 W**



### AREAS OF APPLICATION

- Replacement for floodlights with halogen lamps
- Garages
- Public areas
- Building facades
- Construction areas
- D-sign according to EN 60598-2-24 for fire-risk commercial unit, f. e. by accumulation of dust

### PRODUCT BENEFITS

- Frosted cover made of tempered glass for uniform illumination
- Optimized weight and size due to compact design
- No upper light output ratio (ULOR 0%) when mounted at 0° tilt
- Energy savings of up to 90 % compared to halogen lamp floodlights
- 5 years guarantee

### PRODUCT FEATURES

- Luminaire efficacy: up to 110 lm/W
- Symmetrical beam angle: 100° x 100°
- Mounting bracket for up to 180° tilting
- Type of protection: IP65
- Impact resistance: IK08
- Ambient temperature in operation: -20...+50 °C
- Connection via 1 m cable, wiring required



## TECHNICAL DATA

### Electrical data

Nominal wattage	180.00 W
Operating mode	Integrated LED driver
Nominal voltage	220...240 V
Power factor $\lambda$	> 0.90
Mains frequency	50/60 Hz
Inrush current	68.0 A
Total harmonic distortion	< 20 %
Inrush current time $T_{h50}$	1000 $\mu$ s

### Luminaire control gear data

Output current	790 mA
Max. no. of lum. on circuit break. B16 A	10
Max. no. of lum. on circuit break. C10 A	8
Max. no. of lum. on circuit break. C16 A	13


### Photometrical data

Color temperature	3000 K
Luminous flux	18900 lm
Luminous efficacy	105 lm/W
Standard deviation of color matching	$\leq 5$ sdcn
Light color (designation)	Warm White
Color rendering index Ra	$\geq 80$

### Light technical data

Beam angle	100 ° x 100 °
------------	---------------

### Dimensions & weight



<b>Length</b>	340.0 mm
<b>Width</b>	310.0 mm
<b>Height</b>	81.0 mm
<b>Product weight</b>	4900.00 g
<b>Cable length</b>	1000 mm

### Colors & materials

<b>Body material</b>	Aluminum
<b>Housing color</b>	Black
<b>Product color</b>	Black
<b>Housing color</b>	Black
<b>Cover material</b>	Tempered glass

### Temperatures & operating conditions

<b>Ambient temperature range</b>	-20...+50 °C
----------------------------------	--------------

### Lifespan

<b>Number of switching cycles</b>	100000
<b>Lifespan L70/B50 at 25 °C</b>	50000 h
<b>Lifespan L80/B10 at 25 °C</b>	30000 h
<b>Lifespan L90/B10 at 25 °C</b>	15000 h

### Additional product data

<b>Mounting type</b>	Surface
<b>Mounting location</b>	Wall / Pole / Floor / Ceiling
<b>Product remark</b>	Available from November 2019

### Capabilities


<b>Adjustable</b>	Yes
<b>Dimmable</b>	No
<b>Type of connection</b>	Cable, 3-pole
<b>LED module replaceable</b>	Not replaceable

### Certificates & standards

<b>Protection class IK (shock resistance)</b>	IK08
<b>Glow Wire Test according to IEC 695-2-1</b>	650 °C
<b>Photobiological safety group EN62778</b>	RG 1
<b>Photobio. safety group acc. to EN62471</b>	RG 0
<b>Protection class</b>	I
<b>Type of protection</b>	IP65

<b>Luminaire with limited surface temperature, class "D"</b>	Yes
<b>Standards</b>	CE/CB/TÜV SÜD/EAC/RoHS

## Light Distribution



LDC typ cone

LDC typ polar

## LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075352162	Shipping carton box 1	423 mm x 355 mm x 144 mm	5710.00 g	21.62 dm <sup>3</sup>

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

## REFERENCES / LINKS

For Guarantee see

► [www.ledvance.com/guarantee](http://www.ledvance.com/guarantee)

## DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.