

Vacuum Cleaner LXT®

DCL286F

18V, 180 mbar, 0,25 L, Cyclone

Model DCL286F is a cordless cleaner powered by 18V LXT® Li-Ion battery.

Main features and benefits are: Switch: One-touch push button, Dust collection system: Integrated cyclone unit., 4-suction power mode selection with mode memory function.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Brushless Motor	✓
Air volume	1,0 m³/min
Max. sealed suction	180 mbar
Continuous Use 18V / 6.0 Ah Battery	76 / 42 / 30 / 16 min
Tank Capacity for Dust	0,25 L
Sound Pressure Level (L _{pA})	55 / 60 / 62 / 66 dB (A)
Vibration Level (3 axes)	0,1 m/s²
Tool weight with battery	1,6 - 1,9 kg
Product Dimensions (L x W x H):	1106 x 113 x 177 mm
Continuous Use 18V / 3.0 Ah Battery	38 / 21 / 15 / 8 min
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Suction power	15 / 35 / 60 / 100 W
Product net weight	1,2 kg

User benefits

- Battery protection circuit protects against overloading, over-discharging and over-heating
- Ergonomic soft grip handle provides increased comfort
- Quiet cleaning achieved by redesigning air flow structure

Link to product - www.makitauk.com



Related products

Optional AC

123539-7 Floor T-Nozzle 225 mm, Black		127828-2 Nozzle Assembly	
140H94-2 Soft Brush 360 Complete Set, Blue		140H95-0 Seat Nozzle, Ø32 Mm	
1910D5-0 Cyclone Pre-separator		191D65-8 Long sash nozzle	
191D73-9 Cyclone Pre-Separator 400 ml		191D77-1 Straight Pipe	
191E30-3 Flexible Hose Set		191G86-8 Nozzle assembly set	
458942-6 Suction Tube With Pipe Lock		459038-6 Nozzle Holder Black	

Other

User manual

Parts drawing