

CUC-MP-J1ST-A/4R4LT - RJ45 PCB connector



1149851

<https://www.phoenixcontact.com/gb/products/1149851>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

RJ45 PCB connector, degree of protection: IP20, number of positions: 8, 10 Gbps, material: Metal, connection method: THT wave



Your advantages

- The right version for every application. Available with and without LED, single- and multi-port
- The extended temperature range from -40 °C to +85 °C enables use in demanding applications
- Through-hole technology (THT) provides high mechanical stability when connecting the female connector to the PCB

Commercial data

Item number	1149851
Packing unit	30 pc
Minimum order quantity	30 pc
Sales key	ABNADA
Product key	ABNADA
GTIN	4063151145859
Weight per piece (including packing)	16.963 g
Weight per piece (excluding packing)	16.963 g
Customs tariff number	85366930
Country of origin	TW

CUC-MP-J1ST-A/4R4LT - RJ45 PCB connector



1149851

<https://www.phoenixcontact.com/gb/products/1149851>

Technical data

Product properties

Product type	Data connector (device side)
Type	RJ45
Number of positions	8
Connection profile	RJ45
Type of packaging	Tray
Housing shield springs	Yes
Number of slots	4
Type	Socket
Shielded	yes

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/2)	72 V DC
Rated surge voltage	1.5 kV DC
Rated surge voltage (III/3)	1.5 kV
Rated surge voltage	1 kV DC
Rated current	1.5 A
Frequency range	10 Hz ... 500 Hz
Insulation resistance	> 500 MΩ
Test voltage	1 kV DC
Test voltage Core/Core	1 kV DC
Test voltage Core/Shield	1.50 kV DC
Transmission medium	Copper
Transmission speed	10 Gbps
Power transmission	PoE++

Connection data

Connection technology

Connection method	THT wave
-------------------	----------

Dimensions

Width	63.76 mm
Height	13.3 mm
Length	15.75 mm
Installed height	13.68 mm
Orientation to PCB	90.00 °
Data pin length	2.54 mm

CUC-MP-J1ST-A/4R4LT - RJ45 PCB connector



1149851

<https://www.phoenixcontact.com/gb/products/1149851>

Material specifications

Material Metal surface contact area (top layer)	Au (0.152 µm/6 µ")
Material Metal surface contact area (middle layer)	Ni (1.27 µm/50 µ")
Material Metal surface soldering area (middle layer)	Ni (1.27 µm/50 µ")
Material	Copper alloy (Housing (shielding))
Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	Ni
Contact material	Phosphor bronze
Contact surface material	Gold
Contact carrier material	PA 9T GF

Cable/line

Test voltage Core/Core	1 kV DC
Test voltage Core/Shield	1.50 kV DC
Halogen-free	no
Flame resistance	UL 94 V0

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 750
Insertion force per signal contact	< 20.00 N
Extraction force per signal contact	< 20 N

Environmental and real-life conditions

Test specification

Frequency	10-500 Hz
Sweep speed	1 octave/min
Amplitude	0.35 mm
Acceleration	50.00 m/s ²
Test duration	20.00 s

Test specification

Specification	IEC60068-2-27
Acceleration	295.00 m/s ²

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Standards and regulations

Flame resistance	UL 94 V0
------------------	----------

CUC-MP-J1ST-A/4R4LT - RJ45 PCB connector




1149851

<https://www.phoenixcontact.com/gb/products/1149851>

Mounting

Mounting type	Wave soldering
Processing notes	
Classification temperature T _c	260 °C

Drawings



Classification wave soldering profile

CUC-MP-J1ST-A/4R4LT - RJ45 PCB connector



1149851

<https://www.phoenixcontact.com/gb/products/1149851>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1149851>



cUL Recognized
Approval ID: FILE E 335024



UL Recognized
Approval ID: FILE E 335024

CUC-MP-J1ST-A/4R4LT - RJ45 PCB connector



1149851

<https://www.phoenixcontact.com/gb/products/1149851>

Classifications

ECLASS

ECLASS-13.0	27460201
-------------	----------

ETIM

ETIM 9.0	EC002637
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CUC-MP-J1ST-A/4R4LT - RJ45 PCB connector



1149851

<https://www.phoenixcontact.com/gb/products/1149851>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk