








CAPPED VIEW




REAR VIEW



RECOMMEND MINIMUM MOUNTING PITCH



PCB LAYOUT
CONNECTOR SIDE



RECOMMEND PANEL CUT OUT

REV	DESCRIPTION	DATE	BY	ECN
1	FIRST ISSUE	15-05-23	MH	----
2	CHANGE LATCHING MECHANISM	10-05-24	MH	4950
3	CORRECT CONTACT HEIGHT TO 24.15MM	18-03-25	MH	9754

NOTE:
1. MATING CONNECTOR SHELL TO HAVE MIN 1.6 SURFACE FINISH TO ACHIEVE IP RATING OF THIS CONNECTOR.
2. BLACK MOUNTING SCREW 52500011-430 x 4 PCS TO BE SUPPLIED WITH THE CONNECTOR, MAX TORQUE 0.5Nm.
3. DUE TO 0.4mm THICK RUBBER SEAL, THE DIM WILL VARY DEPENDING ON THE SCREWS TIGHTENING IN ASSEMBLY.

3	55011487-013/913	AXS3FH1V WITHOUT RUBBER FLANGE - TIN/GOLD PLATED CONTACT	1
2	52730032-000	AXS OVERMOLDED RUBBER FLANGE BLACK	1
1	52500011-430	SELF TAPPING SCREW 2.9 x 1.06mm BLACK	4
ITEM	PART NUMBER	DESCRIPTION	QTY

UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE		THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD. NO PART THEREOF MAY BE REPRODUCED AND USED WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER			
LINEAR	ANGULAR	MATERIAL: SEE COMPONENT			
X ± 0.5	X' ± 1	DRN: M.H	DATE: 15-05-23	TITLE: AXS3FP1V AXS PANEL MOUNT SERIES CUSTOMER DRAWING	
X.X ± 0.2	X.X' ± 30'	CKD: M.H	DATE: 18-03-25		
X.XX ± 0.1	X.XX' ± 15'	APP'D: P.M	DATE: 18-03-25		
BREAK ALL SHARP EDGES AND REMOVE ALL BURRS		FINISH: SEE COMPONENT		PART No. SEE TABLE	
DO NOT SCALE		SCALE: 1:1		DRAWING No. 55011487-813-2	
DIMENSIONS IN MILLIMETRES		THIRD ANGLE PROJECTION		SHEET 2/2	

Amphenol Amphenol Australia Pty.Ltd,
22 Industry Blvd, Carrum Downs, VIC 3201