Technical sheet


BTC60BAT


Modular barrier Ø 60mm – swing gate

Modular warehouse barrier designed to ensure safety in industrial areas. It helps to organise vehicle traffic and demarcate high-risk zones, whilst ensuring the protection of people. Made from galvanised steel and coated with yellow epoxy paint. These various components allow for the creation of 'customized' paths:

- Available in 40 mm or 60 mm diameter tubing,
- Various post types: straight, corner, 2-sided or 3-sided,
- Various gate types: wicket gate or swing gate

Fixings available as options.





Customs code	7326909890
EAN	3321360116413

Color : Yellow

Material : Galvanized steel

Specifications :

- Two-way swing door compatible with modular barriers.
- Tube diameter: 60 mm.
- Fitted with a removable stop to secure the door if required.
- Includes a 25 x 28 cm plate.
- Offset mounting plate (150 x 150 mm) with 4 holes (Ø 14 mm).
- Fixings available as an option.
- Do not install in saline or hydrocarbon environments.

Length (mm)	Width (mm)	Height (mm)	Dimensions plate (mm)	Net weight (kg)
930	150	1000	150 x 150	10,50

VISO
www.viso-cpn.com

VISO - 7 avenue Arago - ZI de la Vigne aux Loups - 91380 CHILLY-MAZARIN - France
Tél. + 33 (0)1 69 53 46 70 - Fax + 33 (0)1 69 53 46 80 - contact@viso-cpn.com / commande@viso-cpn.com