



ALL MX FUEL BATTERIES FIT ALL MX FUEL CHARGERS AND EQUIPMENT

	REDLITHIUM FORGE MOST POWER FASTEST CHARGING LONGEST LIFE		REDLITHIUM	
	FORGE 12.0 (MXF HD812)	FORGE 8.0 (MXF XC608)	REDLITHIUM 6.0 (MXF XC406)	REDLITHIUM 3.0 (MXF CP203)
 SUPERCHARGER MXF SC	65 MIN	45 MIN	45 MIN	45 MIN
 STANDARD CHARGER MXF C	160 MIN	110 MIN	90 MIN	45 MIN

Non COOL-CYCLE batteries will continue to charge on MX FUEL charger but will not experience additional cooling effects



EQUIPMENT REDEFINED
TRADE FOCUSED
SYSTEM WIDE

MILWAUKEE TOOL

Milwaukee Electric Tool Corporation
BROOKFIELD, WI 53005
USA
Tel: +1 (262) 781-3600 • Fax: +1 (262) 790-6333

Milwaukee Asia Office
29/F, Tower 2, Kowloon Commerce Centre,
51 Kwai Cheong Road, Kwai Chung, Hong Kong
Tel: +852-2492-2181 • Fax: +852-2490-4778

Distributed by:


6/11/2023

All data incl. service and warranty conditions as well as product range are subject to change without notice. Pictures not binding. No liability for printing errors or mistakes. © 2023 Milwaukee Electric Tool Corporation. All trademarks are owned by Techtronic Cordless GP unless otherwise stated.


www.milwaukeetool.asia




EQUIPMENT REDEFINED
TRADE FOCUSED
SYSTEM WIDE



REDLITHIUM™
BATTERY PACK



REDLINK PLUS™
INTELLIGENCE



POWERSTATE™
BRUSHLESS MOTOR

MXF COS350G2
MX FUEL
350MM
CUT-OFF
SAW

350MM
GAS
PERFORMANCE
NO GAS
HEADACHES

RAPIDSTOP
BLADE BRAKE &
KICKBACK CONTROL

4.3M
IN CONCRETE
120 CUTS
IN REBAR
PER CHARGE



THIS IS EQUIPMENT REDEFINED.

The MX FUEL Equipment System revolutionizes the light equipment market by delivering the performance, run-time and durability demanded by the trades without the hazards associated with emissions, noise, vibration and the frustrations of gas maintenance. This completely compatible system goes beyond the limitations of gasoline and power-cord units, utilizing an advanced batteries, motors and electronics to deliver a high experience for users.



ELECTRIC WATER VALVE

Trigger Activated

LOAD LIGHT INDICATOR

Guides operator force

ON TOOL STORAGE

Scrench for blade changes and allen wrench stored on-board

RAPIDSTOP BLADE BRAKE & KICKBACK CONTROL

Enhanced control

350MM BLADE CAPACITY

Full 124mm cut depth



Diamond Blade Included

ADJUSTABLE BLADE GUARD

Infinite position; increased cut range

GUIDE WHEELS

For smoother, easier cuts

20/25.4/27MM ARBOR ADAPTER

2-in-1 arbor adapters work with 20mm, 25.4mm and 27mm blade arbors

MX FUEL 350MM CUT-OFF SAW (WITH 2 XC608 BATTERIES)



ADDITIONAL EQUIPMENT

3105

Cut-Off Saw Cart



M18 BPFP-WST & M18 BPFPH

M18 SWITCH TANK 15L Backpack Water Supply & Powered Base




ACCESSORIES



PREMIUM DIAMOND BLADE FOR CONCRETE
4932471985



MPP DIAMOND BLADE FOR CONCRETE
4932471986



STEELHEAD BLADE
4932471988




MX FUEL 350MM CUT-OFF SAW

350MM GAS PERFORMANCE NO GAS HEADACHES

ENCLOSED SPACES	Emissions Free
THROTTLE RESPONSE	Instant
MAINTENANCE	No Engine Maintenance


- 350mm gas saw performance
- Safe to use indoor/outdoor
- No engine maintenance
- Up to 50% less noise

RAPIDSTOP BLADE BRAKE & KICKBACK CONTROL



- RAPIDSTOP brake
- Kickback control
- Electric water valve
- Load light indicator to optimize runtime and accessory life
- Enhanced safety

4.3M IN CONCRETE 120 CUTS IN REBAR PER CHARGE



- 350mm blade; 124mm cut depth
- 4.3m fully plunged in concrete
- 120 cuts in rebar



SPECIFICATIONS

DESCRIPTION	SPECIFICATIONS
Rated Speed	5370 min ⁻¹
Cutting disc diameter	350 mm
Maximum cutting depth	124 mm
Arbor size	20 / 25.4 / 27 mm
Bare tool weight	8.95 kg
Weight (w/ 8.0 Ah Battery)	13.3 kg
Dimensions (LxWxH)	787 x 254 x 404 mm