



Connectors > D-Shaped Connectors > D-Sub Connectors > IDC D-Sub Connectors > IDC D-Sub: Receptacle Assembly, Panel Mount, Signal, 1.27 mm



Connector & Housing Type: **Receptacle**

Solid Wire Size: **.05 – .1 mm²**

Shielded: **No**

Connector System: **Cable-to-Panel**

[All IDC D-Sub: Receptacle Assembly, Panel Mount, Signal, 1.27 mm \(11\)](#)

Features

Product Type Features

Connector & Housing Type	Receptacle
Connector System	Cable-to-Panel
Connector Product Type	Connector Assembly
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	50
Number of Rows	2
Compatible With Wire & Cable Type	Ribbon Cable, Round Jacketed Cable

Body Features

Cover Material	Thermoplastic
Shell Plating Material	Nickel over Copper
Ribbon Cable Centerline Spacing	.64 mm[.025 in]
Primary Product Color	Black



Contact Features

Contact Underplating Material	Palladium Nickel
	30 µin
Wire Contact Termination Area Plating Material	Tin-Lead
Contact Options	Installed
Contact Mating Area Plating Material	Gold or Gold Flash
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	1 A

Termination Features

Termination Cover Method	Assembled
Termination Cover Type	Non Lacing
Termination Cover	With
Termination Method to Wire & Cable	Insulation Displacement (IDC)

Mechanical Attachment

Mating Retention Type	Latch Blocks
Thread Size	2-56
Mounting Feature Plating Material	Nickel over Copper
Mounting Feature Material	Zinc
Mating Retention	With
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	Thermoplastic
Shell Material	Steel
Centerline (Pitch)	1.27 mm[.05 in]

Dimensions

Compatible Insulation Diameter Range	.74 – .91 mm[.029 – .036 in]
Compatible Insulation Diameter (Max)	.91 mm
Solid Wire Size	.05 – .1 mm²
Wire Size	30 – 28 AWG

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

--	--



Circuit Application	Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	10
Packaging Method	Tube

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 5749210-5
50 50SR CABLE RCPT ASSY



TE Part # 5749080-1
50 50SR BSHLL KIT,M/J-SCR




TE Part # 5-749611-5
50 50SR PANEL MOUNT RCPT, ROHS




TE Part # 5749111-4
50 50SR CABLE PLUG ASSY




TE Part # 5749193-2
50 50SR KIT,ST,UK



TE Part # 5749193-1
50 50SR KIT,ST,UK




TE Part # 749087-2
50SR SCREWLOCK KIT,FEMALE



TE Part # CAT-AM7-22507
IDC D-Sub: Connector Kit, Plug, Signal, 1.27 mm



TE Part # 5749699-5
50 50SR CABLE RCPT KIT



TE Part # 5749889-3
50 50SR KIT,ST,UK




TE Part # 786585-3
50SR SCREWLOCK KIT,BULK,FEMAL



TE Part # 749087-4
50SR SCREWLOCK KIT,FEMALE



TE Part # 749087-1
50SR SCREWLOCK KIT,FEMALE



TE Part # 749087-3
50SR SCREWLOCK KIT,FEMALE




TE Part # 786585-2
50SR SCREWLOCK KIT,FEMALE


Also in the Series | **AMPLIMITE 0.50 Series**




Connector Caps & Covers(20)



Connector Hardware(6)



D-Sub Backshells & Clamps(21)



IDC D-Sub Connectors(69)




PCB D-Sub Connectors(172)

Customers Also Bought




TE Part #5787082-7
68 50SR R/A RCPT ASSY,RDSN L/F



TE Part #5749721-5
50 50SR VERT RCPT ASSY



TE Part #1622883-1
CRG0603 1% 220K



TE Part #1658670-4
PIN CONTACT,22 DF,LP,22-28 AWG



TE Part #786585-2
50SR SCREWLOCK KIT,FEMALE



TE Part #5227661-1
BNC PCB RT ANGLE




TE Part #1676250-2
RN 0805 20K 0.1% 10PPM 1KRL



TE Part #1-1393560-8
V42254A 122V 1=SUB D BOLZENZA



TE Part #350210-1
03P CMNL HDR ASSY PC NATL



TE Part #341002-1
PL 250 REC TERMINAL 18-14 AWG BR LP

Documents

Product Drawings

50 50SR PANEL MOUNT RCPT

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_1-749656-1_N.2d_dxf.zip



English

Customer View Model

[ENG_CVM_1-749656-1_N.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1-749656-1_N.3d_stp.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-749656-1_L.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-749656-1_L.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-749656-1_L.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPLIMITE Subminiature D Connectors - .050 Series Connector](#)

English

[AMPLIMITE .050 Series D-sub Connectors QRG](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL](#)

English