


FEATURES

- **Material:** Fluorinated Ethylene Propylene and Viton: Provides excellent chemical resistance and durability
- **Hardness:** Shore A 90 to 95: Ensures a firm yet flexible seal
- **Temperature Range:** -20 °C to 140 °C: Suitable for a wide range of operating conditions
- **Inside Diameter:** 101.32 mm: Fits standard applications
- **Thickness:** 1.78 mm: Offers a compact and effective sealing solution

RS PRO 101.32 mm O-Ring Seal, Fluorinated Ethylene Propylene

RS Stock No: 732-018



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO O-Ring Seal is designed for reliable sealing in a variety of industrial applications. Made from high-quality materials including Fluorinated Ethylene Propylene and Viton, it ensures excellent chemical resistance and durability. Ideal for environments requiring robust sealing solutions, it operates efficiently across a wide temperature range.

General Specifications

Colour	Black
Hardness	Shore A 90 to 95
Product Type	O-Ring Seal
Sub Type	O-Ring

Mechanical Specifications

Inside Diameter	101.32 mm
Material	Fluorinated Ethylene Propylene, Fluoroelastomer, Viton
Outside Diameter	104.88 mm
Thickness	1.78 mm

Operation Environment Specifications

Maximum Operating Temperature	140 °C
Minimum Operating Temperature	-20 °C

Approvals

Standards/Approvals	BS ISO 3601-1, AS 568, EC 1935:2004, FDA, ISO 14001:2015, ISO 45001:2015, ISO 9001:2015, LABS, TSCA, USP Class VI, WRAS
---------------------	---

