



The special line for craftsmen and industrial applications. Due to the fact that different materials impose different demands, DRONCO produces discs especially matching the respective material. Special types of corundum and bonds are combined to suit the task in hand. This optimises performance, extends service life, increases efficiency and reduces cutting time.

- manufactured according to EN 12413
- complies to oSa regulations
- of course: Made in Germany

AS 46 Characteristics:
INOX Free of iron and sulphur. Requiring little effort, the special thin cutting disc is easy on man and machine.
High cutting speed, long service life, hardly any burring.

Field of Application:
Normal steel and stainless steel, particularly suitable for sheet metal and thin-walled profiles. The standard disc used on tank farms and in tank construction.

Dimensions [mm]	Dimensions [Inch]	Speed [r.p.m.]	Form	Unit pack	Art. No.	EAN [4081600]
115 x 1,6 x 22,2	4 1/2 x 1/16 x 7/8	13280		25	1111250	111118
125 x 1,6 x 22,2	5 x 1/16 x 7/8	12200		25	1121250	121117
150 x 1,6 x 22,2	6 x 1/16 x 7/8	10200		25	1153250	133103
180 x 1,6 x 22,2	7 x 1/16 x 7/8	8600		25	1183250	143119
230 x 1,9 x 22,2	9 x 5/64 x 7/8	6600		25	1233250	153118