1-322338-1 SUPERSEDED


STRATO-THERM DIAMOND GRIP

TE Internal #: 1-322338-1

TE Internal Description: DG 16-14 HT ALUMEL R 8

View on TE.com >

Terminals & Splices > Ring Terminals




Ring Terminal Product Type: **Closed Ring Tongue Terminal**

Wire Size: **2050 – 5180 CMA**

Stud Size: **#8, M4**

Features

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#8, M4
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Number of Holes	1

Body Features

Product Weight	.315 g
Insulation Sleeve Color	Green
Stripe Color	Green

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Unplated

Mechanical Attachment

Wire Insulation Support	With

Dimensions

Wire Size	2050 – 5180 CMA
Stud Diameter	4.34 mm[.171 in]
Tongue Thickness	.79 mm[.031 in]
Product Length	20.6 mm[.811 in]
Compatible Insulation Diameter (Max)	4.32 mm[.17 in]
Compatible Insulation Diameter Range	3.05 – 4.32 mm[.12 – .17 in]

Usage Conditions

Insulation Option	Uninsulated

Operation/Application

Compatible With Wire Base Material	Nickel

Industry Standards

Government Qualified Terminal	No

Packaging Features

Packaging Quantity	500
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these

limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Also in the Series | STRATO-THERM DIAMOND GRIP



Knife Disconnects(3)



Ring Terminals(60)



Splices(8)


Customers Also Bought




TE Part #1841-1-5620
CONT PIN



TE Part #5205729-1
CLAMSHELL ASSEMBLY,SIZE 1



TE Part #6-1617760-7
FCB-405-0521M=M83536/5-021M



TE Part #814727-000
222A132-4/42-0



TE Part #66259-2
MALE CONTACT ASSY. (L.P.)



TE Part #1757819-3
AMPLIMITE,ASY,PLUG,STD,109,ZN,3



TE Part #CAT-P592-R472A
PIDG Ring Tongue Terminals



TE Part #472967-000
CTC-0018-22-9/5-9CS2340

TE Part #ZPF000000000000861
057-0289-00 B

Documents

Product Drawings

DG 16-14 HT ALUMEL R 8

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-322338-1_AC.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-322338-1_AC.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-322338-1_AC.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Specifications

Application Specification

English