

The 660MBX smoke alarm is a mains powered optical alarm with 9V alkaline battery back up that will provide power to the unit in the event of a mains failure. Up to 12 compatible smoke and heat alarms can be linked for simultaneous warning.



Product features:

- 230V mains powered smoke alarm
- 9V alkaline battery back-up
- Thermally enhanced optical technology
- Test and alarm pause button
- Low battery warning
- Multi-alarm interlink
- LED operating indicators
- Alarm source indicator
- 5 year guarantee
- BS EN 14604: 2005

Model number	660MBX
Description	230V smoke alarm
Technology	Thermally enhanced optical technology
Sensitivity	N/A
Alarm sound level	85dB at 3m
Battery type	9V alkaline battery
Operation AC/DC	AC
Installation positions	Ceiling
Operating temperature	+5°C to +38°C
Operating humidity	10% to 85% relative
Storage temperature	+5°C to +38°C
Storage humidity	10% to 85% relative
Warranty	5 years

Dimensions	140mm (diameter) x 44mm (depth)
Unit weight	224g
Pack dimensions	141mm (H) x 141mm (W) x 48mm (D)
Pack weight	332g
Master pack quantity	10
Master pack dimensions	306mm (H) x 150mm (W) x 256mm (D)
Master pack weight	3.31kg
Pack barcode	00029054019769
Outer barcode	10029054019766
Approvals	BS EN 14604: 2005