

Dust Extractor LXT®

DVC156L

18V X 2 • 110 mbar • 15 l • L

Machine-connectable dust extractor for cleaning or dust removal

A versatile dry dust extractor that runs on two 18V LXT® batteries. Matches filter class 'L'. Run time with 5.0 Ah batteries is about 40 min.



Technical specifications

Nominal Battery Voltage	2 x 18 V
Voltage LXT	✓
Brushless Motor	✓
Air volume	2,1 m³/min
Max. sealed suction	110 mbar
Vacuum hose length	1,7 m
Vacuum hose diameter	32 mm
Tank Capacity for Dust	15 L
Sound Pressure Level (L _{pA})	≤ 70 dB(A)
Noise Uncertainty (K Factor)	2,5 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s²
Vibration Uncertainty (K Factor)	1,5 m/s²
Dust Class	L
Tool weight with battery	7,3 - 7,9 kg
Product Dimensions (L x W x H):	366 x 334 x 421 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion

User benefits

- Brushless maintenance-free and long-life motor
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Low noise level for pleasant work.
- Low power consumption thanks to brushless motor
- Approved for Dust Class L in accordance with the EU standard
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing