

Uninterruptible power supply - UNO-UPS/24DC/24DC/60W - 2905907

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Uninterruptible energy supply with integrated energy storage, lead AGM, VRLA technology, 24 V DC, 0.8 Ah.

Product Description


UPS modules with integrated energy storage are particularly space saving: UPS module and energy storage are combined in one housing. It's just a case of connecting a power supply upstream.

Why buy this product

- Compact and narrow



Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 007380
GTIN	4055626007380
Weight per Piece (excluding packing)	1,100.000 g
Custom tariff number	85371091
Country of origin	Germany

Technical data

Dimensions

Width	110 mm
Height	90 mm
Depth	84 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-15 °C ... 50 °C

Uninterruptible power supply - UNO-UPS/24DC/24DC/60W - 2905907

Technical data

Ambient conditions

Ambient temperature (storage/transport)	-20 °C ... 60 °C
Max. permissible relative humidity (operation)	≤ 95 % (at 25 °C, non-condensing)
Degree of pollution	2

Input data

Input voltage	24 V DC
Nominal input voltage	24 V DC (SELV)
Input voltage range	22.5 V DC ... 29.5 V DC
Current consumption (maximum)	2.8 A
Current consumption (idle)	< 60 mA
Current consumption (charging process)	< 300 mA
Input fuse, integrated	5 A (electronic)

Output data (24 V DC mains operation)

Nominal output current (I _N)	2.5 A
--	-------

Output data (24 V DC battery operation)

Nominal output current (I _N)	2.5 A
--	-------

General output data

Efficiency	> 95 % (Mains operation, with charged energy storage)
------------	---

General

IQ technology	no
Net weight	1 kg
Memory medium	Lead rechargeable battery module
Protection class	III
MTBF (IEC 61709, SN 29500)	> 1900000 h (40 °C)
Mounting position	horizontal DIN rail NS 35, EN 60715
Assembly instructions	Alignable: 0 mm horizontally, 30 mm vertically

Connection data, input

Connection method	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section flexible min.	0.2 mm ²
Conductor cross section flexible max.	2.5 mm ²
Conductor cross section AWG min.	24
Conductor cross section AWG max.	14
Stripping length	7 mm
Screw thread	M3

Uninterruptible power supply - UNO-UPS/24DC/24DC/60W - 2905907

Technical data

Connection data, output

Connection method	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section flexible min.	0.2 mm ²
Conductor cross section flexible max.	2.5 mm ²
Conductor cross section AWG min.	24
Conductor cross section AWG max.	14
Stripping length	7 mm
Screw thread	M3

Connection data for signaling

Connection method	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section flexible min.	0.2 mm ²
Conductor cross section flexible max.	2.5 mm ²
Conductor cross section AWG min.	24
Conductor cross section AWG max.	14
Stripping length	7 mm
Screw thread	M3

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise immunity	EN 61000-6-2
Standards/regulations	EN 61000-4-2
Contact discharge	4 kV (Test Level 2)
Standards/regulations	EN 61000-4-3
Frequency range	80 MHz ... 3 GHz
Test field strength	10 V/m (Test Level 3)
Standards/regulations	EN 61000-4-4
Comments	Criterion B
Standards/regulations	EN 61000-4-5
Signal	1 kV (Test Level 2 - asymmetrical)
Standards/regulations	EN 61000-4-6
Frequency range	0.15 MHz ... 80 MHz
Voltage	10 V (Test Level 3)
Standard - Electrical safety	EN 60950-1/VDE 0805 (SELV)
Standard – Electronic equipment for use in electrical power installations and their assembly into electrical power installations	EN 50178/VDE 0160 (PELV)

Uninterruptible power supply - UNO-UPS/24DC/24DC/60W - 2905907

Technical data

Standards and Regulations


UL approvals	UL Listed UL 508
	UL/C-UL Recognized UL 60950-1
Shock	18 ms, 30g, in each space direction (according to IEC 60068-2-27)
Vibration (operation)	< 13.2 Hz, amplitude ±1.0 mm (according to IEC 60068-2-6)
	13.2 Hz ... 100 Hz, 0.7g

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 25;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Block diagram



Classifications

eCl@ss

eCl@ss 5.1	27040603
eCl@ss 6.0	27040603
eCl@ss 8.0	27040603
eCl@ss 9.0	27040705

ETIM

ETIM 5.0	EC000382
ETIM 6.0	EC000382

UNSPSC

UNSPSC 13.2	39121011
-------------	----------

Approvals

Approvals

Uninterruptible power supply - UNO-UPS/24DC/24DC/60W - 2905907

Approvals

Approvals

UL Listed / cUL Listed / EAC / IECEE CB Scheme / UL Recognized / cUL Recognized / cULus Recognized

Ex Approvals

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 123528
cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 123528
EAC			RU C- DE.A*30.B.01082
IECEE CB Scheme		http://www.iecee.org/	DK-47330-A1-UL
UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 214596
cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 214596
cULus Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	

Uninterruptible power supply - UNO-UPS/24DC/24DC/60W - 2905907

Accessories

Accessories

Power supply

Power supply unit - UNO-PS/1AC/24DC/ 60W - 2902992



Primary-switched UNO POWER power supply for DIN rail mounting, input: 1-phase, output: 24 V DC/60 W

Power supply unit - UNO-PS/1AC/24DC/100W - 2902993



Primary-switched UNO POWER power supply for DIN rail mounting, input: 1-phase, output: 24 V DC/100 W
