

IPD WD 5P2,5 1,0 M25 GY - Panel feed-through



1047364

<https://www.phoenixcontact.com/in/products/1047364>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Panel feed-through, Direct connection, product family: IPD, connection method: Single wires/ Push-in connection, number of positions: 4+PE, M25, 0.5 mm² ... 2.5 mm², 450 V, 16 A, PA, light gray, external cable diameter: 7 mm ... 11 mm and 11 mm ... 16 mm, cable length: 1 m

Your advantages

- Convenient: quick and easy assembly without special tools
- Fast and easy startup, thanks to tool-free Push-in connection technology
- Reliable installation in harsh environments with IP66, IP68, and IP69K throughout the entire system

Commercial data

Item number	1047364
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	AF6ICB
Catalog page	Page 469 (C-2-2019)
GTIN	4055626648514
Weight per piece (including packing)	231.7 g
Weight per piece (excluding packing)	231.7 g
Customs tariff number	85366990
Country of origin	CN

IPD WD 5P2,5 1,0 M25 GY - Panel feed-through



1047364

<https://www.phoenixcontact.com/in/products/1047364>

Technical data

Product properties

Product type	Panel feed-through
Product family	IPD
Number of positions	5
Connection profile	4+PE
Position marking	1, 2, 3, N, PE
Type	Direct connection

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Connection data


Connection technology

Connection method On the device side	Single wires
Connection method On the field side	Push-in connection
Frequency of connections between conductors of the same cross section	max. 10

Conductor connection

Conductor cross section flexibel	0.5 mm ² ... 2.5 mm ²
Conductor cross section solid	0.5 mm ² ... 2.5 mm ²
Conductor cross section with ferrule	0.5 mm ² ... 2.5 mm ²
Connection cross section AWG	20 ... 14

Dimensions

Dimensional drawing	
Width	33 mm
Length	91.8 mm

Electrical properties

Rated surge voltage (III/3)	6 kV
Rated current	16 A
Rated voltage (III/3)	450 V
Nominal voltage U _N	450 V AC 450 V DC
Nominal current I _N	16 A (observe derating)

Mechanical properties

IPD WD 5P2,5 1,0 M25 GY - Panel feed-through



1047364

<https://www.phoenixcontact.com/in/products/1047364>

Mechanical data

Insertion/withdrawal cycles	10
-----------------------------	----

Material specifications

Color (Housing)	light gray (RAL 7035)
Material Housing	PA
Material Seal	NBR (Field)
	EPDM (Device)
Contact material	Cu
Contact surface material	Ni/Sn

Cable/line

Cable length	1 m
External cable diameter	7 mm ... 11 mm
	11 mm ... 16 mm
Stripping length of the individual wire	10 mm
Position marking	1, 2, 3, N, PE
Single wire, color	brown, black, gray, blue, green-yellow
Halogen-free	no

Mounting

Mounting type	Front mounting M25
---------------	--------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
	IP68 (2 m / 24 h)
	IP69K
Impact strength	IK07
Ambient temperature (operation)	-40 °C ... 90 °C (T = 45 °C)
Temperature when conductor connected	-5 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 90 °C
Resistance to UV radiation	yes


IPD WD 5P2,5 1,0 M25 GY - Panel feed-through

1047364

<https://www.phoenixcontact.com/in/products/1047364>


Drawings


Diagram




Derating diagram for 1.0 mm²

Dimensional drawing





Derating diagram for 1.5 mm²



Derating diagram for 2.5 mm²

IPD WD 5P2,5 1,0 M25 GY - Panel feed-through



1047364

<https://www.phoenixcontact.com/in/products/1047364>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1047364>



VDE approval of drawings

Approval ID: 40049992



UL Listed

Approval ID: E468743

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Only rigid conductors	600 V	15 A	-	- 14
multi-stranded with ferrule	600 V	15 A	-	- 14



cUL Listed

Approval ID: E468743

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Only rigid conductors	600 V	17 A	- 14	-
multi-stranded with ferrule	600 V	17 A	- 14	-

DNV

Approval ID: TAE00004G2

cULus Listed

IPD WD 5P2,5 1,0 M25 GY - Panel feed-through



1047364

<https://www.phoenixcontact.com/in/products/1047364>

Classifications

ECLASS

ECLASS-11.0	27440602
ECLASS-12.0	27440602
ECLASS-13.0	27440602

ETIM

ETIM 9.0	EC002566
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

IPD WD 5P2,5 1,0 M25 GY - Panel feed-through



1047364

<https://www.phoenixcontact.com/in/products/1047364>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

IPD WD 5P2,5 1,0 M25 GY - Panel feed-through



1047364

<https://www.phoenixcontact.com/in/products/1047364>

Accessories

SEALING PLUG 14X22 RD - Sealing plug

1400270

<https://www.phoenixcontact.com/in/products/1400270>

Sealing plug, for threads pluggable, color: red



SEALING PLUG 10X16 RD - Sealing plug

1400284

<https://www.phoenixcontact.com/in/products/1400284>

Sealing plug, for threads pluggable, color: red



IPD WD 5P2,5 1,0 M25 GY - Panel feed-through



1047364

<https://www.phoenixcontact.com/in/products/1047364>

ZBF 4:UNBEDRUCKT - Zack Marker strip, flat

0808587

<https://www.phoenixcontact.com/in/products/0808587>




Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, mounting type: latching, for terminal block width: 4 mm, Number of individual labels: 10, text field height: 5.2 mm, text field width: 4.2 mm

UC-TMF 4 - Marker for terminal blocks

0818166

<https://www.phoenixcontact.com/in/products/0818166>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 4.2 mm, Number of individual labels: 120, text field height: 5.1 mm, text field width: 3.6 mm

IPD WD 5P2,5 1,0 M25 GY - Panel feed-through



1047364

<https://www.phoenixcontact.com/in/products/1047364>

UCT-TMF 4 - Marker for terminal blocks

0828742

<https://www.phoenixcontact.com/in/products/0828742>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: latching, for terminal block width: 4.2 mm, Number of individual labels: 90, text field height: 4.7 mm, text field width: 3.4 mm

SZF 1-0,6X3,5 - Screwdriver

1204517

<https://www.phoenixcontact.com/in/products/1204517>



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

IPD WD 5P2,5 1,0 M25 GY - Panel feed-through



1047364

<https://www.phoenixcontact.com/in/products/1047364>

CRIMPFOX CENTRUS 6S - Crimping pliers

1213144

<https://www.phoenixcontact.com/in/products/1213144>



Crimping pliers, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm² ... 6 mm², also for TWIN ferrules up to 2 x 4 mm², automatic cross section adjustment, lateral insertion, equipped with fall protection

QSS 27 - Socket wrench

1670646

<https://www.phoenixcontact.com/in/products/1670646>



Allen wrench, for loosening and fastening the QUICKON union nut, WAF 27 mm

IPD WD 5P2,5 1,0 M25 GY - Panel feed-through



1047364

<https://www.phoenixcontact.com/in/products/1047364>

CRIMPFOX VARIO 4S - Crimping pliers

1108766

<https://www.phoenixcontact.com/in/products/1108766>



Crimping pliers, contact connection type: Insulated and uninsulated ferrules, min. cross section: 0.25 mm², max. cross section: 4 mm², compression: Square crimp, weight 401 g, black/green

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in