PUSH AND GEAR TRAVEL TROLLEYS

Push trolley model HTP

Capacities: 500 - 20000kg

The trolley enables the exact positioning or easy traversing of large loads with either manual or powered hoisting equipment.

Features include:

- It has excellent rolling features due to machined steel wheels mounted on prelubricated, encapsulated ball bearings.
- Adjustable to fit a wide range of beam widths and profiles (e.g. INP, IPE and IPB).
- Adjustments are made by rotating the clevis load bar which also ensures the centred positioning of the hoist in the clevis – no creeping to the left or the right.
- The trolley wheels are designed for a max. beam profile incline of 14 % (DIN 1025 part 1).
- Trolleys are in accordance with the UVV and machinery directives.



Capacity (WLL) kg	Beam width mm	Weight kg
		Type 'A'
500	50 - 220	8.0
1000	50 - 220	9.0
2000	66 - 220	16.0
3000	74 - 220	32.0

90 - 220

48.0

5000

HTP (PUSH TRAVEL)					
	Capacity (WLL)	Beam width	Weight		
	kg	mm	kg		
	Type 'B'				
	500	160 - 300	10.6		
	1000	160 - 300	12.0		
	2000	160 - 300	19.3		
	3000	180 - 300	35.8		
	5000	180 - 300	52.2		